



SkyMast - the perfect complement for StarBay STB-25

SkyMast Lighting System

SkyMast Lighting System enables the luminaires to provide optimum light levels over a large area. SMLS highmast system is designed to accommodate up to twelve fixtures and may be specified to system heights up to 150 feet. An internal hoist assembly is included to allow for ground-level maintenance. Top and bottom latching options are available to properly and securely support the ring assembly at the top of the pole. Accurate highmast pole selection depends on number and type of luminaire specified, as well as luminaire options and shielding. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~b~GT~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

Benefits

- Corrosion-resistant
- Quick and easy lowering and raising of the lighting system ring
- Customize the system to meet your needs

Features

- High strength materials
- Numerous options and accessories available

Application

- Road and Street

SkyMast Lighting System

Versions

