



SL-23 - durable and discreet illumination

SL-23 Composite Inground

The SL-23 is an in-ground commercial luminaire manufactured from compression molded Rhinolite Composite housing, corrosion resistant in harsh lighting environments. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. The ballast compartment is sealed and also separated from the lamp compartment by another anti-wicking chamber. Applications include landscape lighting, architectural lighting, trees, flagpoles, columns, building accents and wallwashing.

Benefits

- Superior durability
- UV and corrosion resistant
- Protected against moisture, dust and insects
- Suitable for a variety of applications

Features

- Structurally reinforced with glass fibers
- Trim ring and debris cover included
- Silicone gasketing
- Available in a variety of optical distributions

Application

- Landscape

SL-23 Composite Inground

Versions

