



SL-25 - durable and discreet illumination

SL-25 Composite Inground

The SL-25 is a small inground luminaire with 6-5/8" footprint. Features include a corrosion resistant direct burial pipe with provision for anti-rotation device. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. The ballast compartment is sealed and also separated from the lamp compartment by another anti-wicking chamber. Applications include pedestrian areas, landscape lighting, trees, flagpoles, columns, building accents, architectural lighting and wallwashing.

Benefits

- Superior durability
- UV and corrosion resistant
- Protected against moisture, dust and insects
- Suitable for a variety of applications

Features

- Low copper, heavy-duty, cast aluminum housing
- Silicone gasketing
- Available in a variety of optical distributions

Application

- Landscape

SL-25 Composite Inground

Versions

