



SL-33 - durable and discreet illumination

SL-33 Composite Inground

The SL-33 inground luminaire is manufactured with a compression molded Rhinolite(TM) Composite housing that is corrosion resistant in harsh landscape lighting environments. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. Applications include landscape lighting, trees, flagpoles, columns, building accents, architectural lighting and wallwashing.

Benefits

- Superior durability
- UV and corrosion resistant
- Protected against moisture, dust and insects
- Suitable for a variety of applications

Features

- Structurally reinforced with glass fibers
- Trim ring and debris cover included
- Silicone gasketing
- Available in a variety of optical distributions

Application

- Landscape