



# SL-34 - durable and discreet illumination

## SL-34 Composite Inground

The SL-34 in-ground luminaire is manufactured with a compression molded Rhinolite Composite housing that is corrosion resistant in harsh landscape lighting environments. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. Applications include landscape lighting, trees, flagpoles, columns, building accents, architectural lighting and wallwashing.

### Benefits

- Superior durability
- UV and corrosion resistant
- Protected against moisture, dust and insects
- Suitable for a variety of applications

### Features

- Structurally reinforced with glass fibers
- Trim ring and debris cover included
- Silicone gasketing
- Available in a variety of optical distributions

### Application

- Landscape

## SL-34 Composite Inground

### Versions

