



SL-42 - durable and discreet illumination

SL-42 Composite Inground

The SL-42 inground luminaire is manufactured with a compression molded Rhinolite composite material, structurally reinforced with glass fibers. It features superior resistance to ultraviolet degradation and corrosion resistant in harsh landscape lighting environments. Other features include two 3/4" NPT conduit entrances, connection to ballast compartment by way of anti-wicking chamber and a junction-box sealed with gasketed die cast aluminum cover plate. Suitable for through wiring.

Benefits

- Superior durability
- UV and corrosion resistant
- Protected against moisture, dust and insects
- Suitable for a variety of applications

Features

- Structurally reinforced with glass fibers
- Trim ring and debris cover included
- Silicone gasketing
- Available in a variety of optical distributions

Application

- Landscape

SL-42 Composite Inground

Versions

