



Leveraging the latest in LED technology and optical enhancements

SlimSurface LED Downlight

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Benefits

- The thinnest available solution with an integral driver for existing J-boxes or new construction
- Provides an affordable alternative to Air-Seal IC recessed housings or Fire-Rated boxes
- Glare controlling lens for comfortable light distribution

Features

- Choice of design with square and round apertures
- Efficacy: 42-70 lm/w
- 50,000 hour rated life
- Dimming: Triac (10%), 0-10V

Application

- Residential
- Office
- Banks
- Hospitality
- Airports
- Fashion
- Arena and Sports

SlimSurface LED Downlight

Versions



S5R830K7

