



SMS – Durable performance

SMS Surface Mount

Designed for smaller, tight spaces or to be hidden from sight in valance or under-shelf applications, the SMS performs perfectly in areas requiring high light level delivery. Wide opening fixture mouth with optional reflectors offer great light spread and throw with the use of a single lamp. This fixture is available in several different lengths that meet custom case design criteria. Most notable about this fixture is the heavy wireguard that can be affixed to the front fixture opening. This adds an additional safety feature offering protection for the lamp in tight design spaces. Applications include cove lighting, display boxes, valances, specialty wall wash applications, shelving units, cabinetry, store displays and anywhere space is limited and resistance to impact is important.

Benefits

- Perfect where space is limited
- Sturdy construction

Features

- Manufactured with all the knockouts necessary for standard surface/corner mounting
- Housing is brake formed from heavy gauge cold rolled steel
- Wire guard is available in either highly polished aluminum or highly reflective white finishes

Application

- Retail
- Office

SMS Surface Mount

Versions

