



# Next generation lighting perfected

## Spot LED – Accessory Holder

Spot LED 10W, 34W, Track & Recessed Lighting, Accessory Holder, Matte White and Matte Black

### Benefits

- A high brightness LED track solution in a multi-optic LED design
- Luminaires range in size, with multiple distributions, lumen packages, color temperatures, beam spreads and finishes
- Trailing edge (ELV) dimming

### Features

- Spot, Narrow Flood and Flood beam spreads
- Available in 600, 1000 and 2000 lumens
- Multiple accessories available to customize the light output and visual appearance of the fixture

### Application

- Fashion
- Food and Large Retailers

## Spot LED - Accessory Holder

### Versions

