



SS Strip -- Low-profile, industrial styling

SS Staggered T5 Strip

Full 10 cm (4") overlap. Eliminates shadows from lamp ends. Housing only 3.7 cm (1-7/16") deep. Safe-handling metal edges. Fully enclosed wire way. Excellent for applications where continuous, even illumination is required.

Benefits

- Uniform lighting
- Easy installation

Features

- Only 1-7/16" deep
- Utilises compact, high-efficiency T5 or T5HO lamps
- 3" lamp overlap for even illumination

Application

- Manufacturing
- Office

SS Staggered T5 Strip

Versions

