



Low profile and tamper resistant

Surface Modular Tamper Resistant

The Surface Modular Tamper Resistant luminaire features a surface mounted low profile body with a tamper resistant door frame and lens options.

Benefits

- Designed to withstand corrosion and tampering
- Suitable for multiple applications to fit many needs

Features

- Tamper resistant door frame and lens
- Housing is multi-stage phosphate treated for maximum corrosion resistance
- K.O.'s provided in ends allows individual or continuous row mounting

Application

- Office
- Banks
- Hospitality
- Petrol and Convenience
- Fashion
- Security Lighting

Surface Modular Tamper Resistant

Versions

