



SV5 Strip – Compact, efficient

SV5 Series

At less than 4" in depth, the SV5 Accessory is perfect for areas that place a premium on low profile appearances to minimize obstruction to the eye in open area settings. Likewise, its ability to be continuous row mounted provides a streamlined form that allows it to be used as a low cost pendant system. Combining the reflector's solid, perforated or slotted materials with the Louver/Lens material options greatly enhances the SV strip's overall appearance and style possibilities. The lay-in louver offers a smooth, low profile blade while the lay-in lens accessory offers two combinations of lens textures— linear ribbed opal and clear linear ribbed. No matter what the choice, light emitted from the fixture is diffused along the entire length of the lens for a glare-free environment.

Benefits

- Multiple mounting options means flexibility for different needs

Features

- Available in lengths of 2', 3', 4' or 8'
- Channel is only 2" wide and 1-5/8" deep
- Surface, pendant or cable mounting
- Suitable for damp locations

Application

- Office
- Banks
- Hospitality
- Education

SV5 Series

Versions

