



T Strip – Economical, functional

T Series T8 Strip

Heavy duty standard cross section strip luminaire offers row, surface or suspension mounting. High reflectance white baked enamel partnered with a variety of reflector options provides outstanding performance.

Benefits

- Multiple mounting options means flexibility for different needs
- Convenient installation

Features


- Available in lengths of 2', 3', 4' or 8'
- Suitable for unit, row, surface or suspension mounting
- Multiple knockouts
- Suitable for damp locations

Application

- Manufacturing
- Industrial
- Office
- Retail

T Series T8 Strip

Versions



T232-347-1/2-EB



T232-UNV-1/2-EB

