



Quality and low-profile

TG8 Recessed Lensed

TG8 Lensed Troffer is a quality low-profile recessed luminaire with specification features. It is designed around T8 lamps and electronic ballasts.

Benefits

- Minimized clearance requirements
- Two finish options means ability to fit many styles

Features


- Housing is constructed of pre-painted steel
- K.O.s provided in each end cap
- Low profile body
- Suitable for damp locations

Application

- Office
- Banks
- Hospitality
- Petrol and Convenience
- Fashion

TG8 Recessed Lensed

Versions



1TG8232-01-UNV-1/2-EB

