



# Cost effective with easy installation

## TR Recessed Retrofit Kit

The TR troffer retrofit kit is designed to offer the end user a cost effective way to increase the efficiency and lumen output of existing troffer fixtures. Applications include warehouse, general lighting, classrooms, gymnasiums and retail applications. TR retrofit kits are available with a variety of lamp and reflector combinations allowing the customer to design the TR system to meet or exceed existing light levels and customize the “look” to match their specific needs. Optimum recommends the coupling of the Enhanced Specular reflector with high lumen T8 lamps as a way to maximize lumen output and fixture efficiency. The TR troffer retrofit is designed for easy installation in existing troffer fixtures.

### Benefits

- Cost effective way to increase the efficiency and lumen output of existing troffer fixtures.

### Features

- Variety of lamp and reflector combinations

### Application

- Education
- Office
- Banks
- Hospitality
- Airports
- Fashion
- Petrol and Convenience

## TR Recessed Retrofit Kit

### Versions

