



# Transit – versatility in action

## Transit LED post top (TR10)

The versatility and character of the Lumec Transit LED post top and pendant luminaires is clear. Combining stunning industrial looks with outstanding photometric performance, the Transit luminaires blend modern and traditional style with leading-edge engineering that have made Lumec luminaires the perfect choice for effective urban area lighting. Comfortable at any mounting height with a broad selection of optics, style options and lumen outputs make the Transit a sensible choice for your project's lighting needs.

### Benefits

- Versatile luminaires available with various style options
- Specific mounting options designed for Transit luminaires maintain harmony in your project's design
- Post top and pendant versions available to suit a wide range of applications
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance

### Features

- Multiple lumen packages with output of up to 7,530 lumens
- Type 2, 3, 4, and 5 optics available
- 4000K and 3000K color temperatures available
- Dimming driver standard
- Maximizes energy savings with multiple driver options and programmed dimming options

### Application

- Road and Street
- Parks and Plazas
- Road and Street
- Parks and Plazas

## Transit LED post top (TR10)

### Versions

