



Cost effective

TR-HVA Recessed Retrofit Kit

The TR HVA retrofit kit is designed to offer the end user a cost effective way to increase the efficiency and lumen output of existing troffer fixtures. Applications include general lighting, classrooms and retail applications. TR HVA retrofit kits are available with a variety of lamp and ballast combinations allowing the customer to design the TR HVA system to meet or exceed existing light levels. The use of a ribbed acrylic center panel provides soft, comfortable illumination. The TR HVA troffer retrofit is designed for easy installation in existing troffer fixtures.

Benefits

- Easy installation in existing troffer fixtures

Features

- Variety of lamp and ballast combinations

Application

- Education
- Office
- Banks
- Hospitality
- Airports
- Fashion
- Petrol and Convenience

TR-HVA Recessed Retrofit Kit

Versions

