



TruGroove - Seamless 3" ribbon of light with exceptional performance and versatility for functional and decorative applications.

TruGroove wall

TruGroove LED is driving performance beyond the edge. Innovative optics deliver exceptional uniformity and wide row spacing from a 3" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Benefits

- Elevated performance to a whole new level in narrow aperture lighting
- Wide row spacing with fewer fixtures and less energy consumption
- Ideal for a variety of applications with multiple distributions and modules

Features

- MesoOptics DX and innovative optics producing optimal batwing distribution
- Symmetric, asymmetric, direct, indirect, direct/indirect and indirect/direct distribution options
- Response Daylight and Actilume Occupancy with field-enabled Daylight sensors
- Multiple lumen package and color temperature options
- Suspended, wall and surface mount versions

Application

- Office
- Banks
- Hospitality
- Fashion
- Education
- Airport

Versions

