



Reflections of Uniformity

Vetro PW Series Wall Sconces

Satin machined aluminum and hand-blown opal glass. A handsome proportion of materials engineered to provide a functional design element and an efficient luminaire.~LT~br~GT~LT~GT~LT~br~GT~LT~br~GT~LT~b~GT~Must order: Power Head and Glass separately.~LT~b~GT~

Benefits

- Cast and machined aluminum with hand blown glass
- 8" or 10" inner element size options
- Glass and acrylic options available

Features

- Family of decorative wall sconces
- Choice of LED, CFL, or INC options

Application

- Fashion
- Office

Versions

