



# Reflections of Uniformity

## Vetro PW Series Wall Sconces

Satin machined aluminum and hand-blown opal glass. A handsome proportion of materials engineered to provide a functional design element and an efficient luminaire.~LT~br~GT~~LT~/~GT~~LT~br~GT~~LT~/br~GT~~LT~b~GT~Must order: Power Head and Glass separately.~LT~/b~GT~

### Benefits

- Cast and machined aluminum with hand blown glass
- 8" or 10" inner element size options
- Glass and acrylic options available

### Features

- Family of decorative wall sconces
- Choice of LED, CFL, or INC options

### Application

- Fashion
- Office

## Vetro PW Series Wall Sconces

### Versions

