



Visualume - subtle design and simple lines

Visualume Tunnel Luminaire (VLM)

Subtle design and simple lines makes the Visualume VLM Series a good choice for tunnels, underpasses, highway entry ways and exits as well as tollbooths. Given the harsh conditions prevailing in their intended environments, luminaires in the Visualume have been developed for physical as well as photometric performance. www.lumec.com/Lumec3Dv3/home/index_en.php
target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Quick and easy maintenance
- Protected against moisture, dust and insects
- Meets ANSI standard for vibration specifications for bridge/overpass applications

Features

- Toolfree access to internal components
- IP66 optical system
- Silicone gasketing

Application

- Road and Street
- Tunnel
- Parking Garages

Visualume Tunnel Luminaire (VLM)

Versions

