



Haute performance et apparence claire

Wal-Lyter LED Recessed Wall Wash

The Day-Brite/CFI Wal-Lyter LED Recessed Wallwash is a high performance luminaire luminaire that delivers good light levels and an even wash of light. Low-iridescent semi-specular reflectors do not protrude below the ceiling line. This provides a clean appearance while controlling the light output of high efficiency LED boards to illuminate vertical surfaces uniformly.

Avantages

- Éclaire uniformément les surfaces verticales ou les écrans
- Faible entretien
- Convient à tous les systèmes de plafonds à ossature encastrée

Fonctions

- Les DEL à haute efficacité ont une durée de vie minimale de 5 heures
- Plaque d'accès homologuée UL
- Installation facile, rapide

Versions

