



# WAM1D/WBM1D LED - offers a variety of lighting design possibilities

## WAM1D/WBM1D Mini Floodlight LED

The WAM1D/WBM1D is a line voltage LED flood light delivering 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80. Construction is die-cast aluminum for durability and it has fully-adjustable swivel arm with vibration-proof locking teeth. Optics include a Clear tempered glass lens.

### Benefits

- Ensures long-lasting durability and reliability
- Able to direct light with ultimate precision
- Completely dust tight and sealed against direct jets of water
- Fade and abrasion resistant
- Offers 50,000 hour life with LED

### Features

- Die cast aluminum housing
- Fully-adjustable swivel arm with vibration-proof locking teeth
- IP66 rated
- Warm or cool color temperatures available
- Clear or frosted tempered lens available

### Application

- Landscape

## WAM1D/WBM1D Mini Floodlight LED

### Versions

