



WAMT14/WBMT14 - offers a variety of lighting design possibilities

WAMT14/WBMT14 Mini Floodlight

The WAMT14 is a line voltage flood light using a 50W maximum T4 halogen lamp. Construction is die-cast aluminum for durability and it has fully-adjustable swivel arm with vibration-proof locking teeth. Optics include a Clear tempered glass lens.

Benefits

- Ensures long-lasting durability and reliability
- Able to direct light with ultimate precision
- Completely dust tight and sealed against direct jets of water
- Fade and abrasion resistant
- Offers 50,000 hour life with LED

Features

- Die cast aluminum housing
- Fully-adjustable swivel arm with vibration-proof locking teeth
- IP66 rated
- Warm or cool color temperatures available
- Clear or frosted tempered lens available

Application

- Landscape

WAMT14/WBMT14 Mini Floodlight

Versions

