



# WP - the industry standard for durability and performance

## WP Wall Pack Large

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

### Benefits

- Minimized glare and uniform light distribution
- Heat and shock resistant
- Increased safety during maintenance
- Durable and reliable construction
- Available with photocell for increased energy savings

### Features

- Permanently bonded borosilicate glass refractor
- Precision die cast aluminum construction
- Stainless steel aircraft cable safety

### Application

- Security Lighting

## WP Wall Pack Large

### Versions

