



WP LED - classic design, improved LED performance

WP Wall Pack Large LED

The Stonco LED wallpack large WP offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced the Philips LEDGINE platform, WP LED provides improved energy savings compared with the former LED design. This versatile luminaire is ideal to match existing fixtures or retrofit HID legacy designs.

Benefits

- Consumes 31 % less energy than previous generation
- Increased lumen output
- Fade and abrasion resistant
- Matches existing luminaires or HID retrofits

Features

- Glass refractor design
- Several controls option available
- One-piece die-cast aluminium housing
- TGIC powdercoat finish

Application

- Security Lighting

WP Wall Pack Large LED

Versions

