



# WP LED - classic design, improved LED performance

## WP Wall Pack Large LED

The Stonco LED wallpack large WP offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced the Philips LEDGINE platform, WP LED provides improved energy savings compared to the former LED design. This versatile luminaire is ideal to match same as existing or retrofit HID legacy designs.

### Benefits

- Consumes 31% less energy than previous generation
- Increased lumen output
- Fade and abrasion resistant
- Matches existing luminaires or HID retrofits

### Features

- Glass refractor design
- Several controls option available
- One-piece die cast aluminum housing
- TGIC powdercoat finish

### Application

- Security Lighting

## WP Wall Pack Large LED

### Versions

