



WPM LED - classic design, improved LED performance

WPM Wall Pack Medium LED

The Stonco LED wallpack medium WPM offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced Philips LED platforms, WPM LED provides improved energy savings compared to the former LED design. This versatile luminaire is ideal to match same as existing or retrofit HID legacy designs

Benefits

- Consumes 43% less energy than previous generation
- Increased lumen output
- Fade and abrasion resistant
- Matches existing luminaires or HID retrofits

Features

- Glass refractor design
- Several controls option available
- One-piece die cast aluminum housing
- TGIC powdercoat finish

Application

- Security Lighting

WPM Wall Pack Medium LED

Versions

