

FlexBlend – Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application


- Offices
- Education
- Healthcare
- Banks

Versions

O FlexBlend Recessed-RC340B
W30L120 MLO VPC




Dimensional drawing



FlexBlend Recessed

Dimensional drawing



Product details

O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC



FlexBlend Recessed-
RC340B_MLO_DPP



FlexBlend Recessed

Product details

FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C




FlexBlend Recessed-
RC340B_W60L60_CPC brackets



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP



0_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed

Product details



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Optic type	Wide beam
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%
Suitable for random switching	Yes

General Information

Order Code	Full Product Name	Glow-wire test	Product family code
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	RC340B
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	RC340B
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	RC340B
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	RC340B
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	RC340B
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	RC340B
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	RC340B
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	RC340B
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	RC340B
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	RC340B
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Temperature 650 °C, duration 30 s	RC340B
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	RC342B
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	RC342B
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	RC340B
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	RC340B
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	RC340B
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	RC340B
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	RC340B
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	RC340B
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	RC340B
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	RC340B

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Product family code
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	RC340B
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	RC340B
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	RC340B
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	RC340B
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	RC340B
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	RC340B
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	RC340B
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	Temperature 850 °C, duration 30 s	RC340B
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B

Order Code	Full Product Name	Glow-wire test	Product family code
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	RC340B
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC342B
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	RC340B
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	RC340B
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	RC340B
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	RC340B
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	RC340B
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	Temperature 650 °C, duration 30 s	RC340B
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s	RC340B
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	RC340B
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	Temperature 650 °C, duration 30 s	RC340B
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	Temperature 650 °C, duration 30 s	RC340B
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	Temperature 850 °C, duration 30 s	RC340B
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	Temperature 850 °C, duration 30 s	RC340B
10429700	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	Temperature 850 °C, duration 30 s	RC340B
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Temperature 650 °C, duration 30 s	RC340B
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	RC342B
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s	RC342B

Light Technical

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	4000 K	≥90	96 lm/W	3,600 lm
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	4000 K	≥90	95.5 lm/W	4,200 lm
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	4000 K	≥90	94.5 lm/W	4,200 lm
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	4000 K	≥90	88 lm/W	3,600 lm
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	86.5 lm/W	3,600 lm
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	4000 K	≥90	87.5 lm/W	4,200 lm
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	85.5 lm/W	4,200 lm
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	96 lm/W	3,600 lm
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	94.5 lm/W	4,200 lm
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	4000 K	≥90	111 lm/W	3,600 lm
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	4000 K	≥90	109 lm/W	3,600 lm
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	4000 K	≥90	127 lm/W	4,200 lm
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	4000 K	≥90	125 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	4000 K	≥90	114 lm/W	4,200 lm
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	4000 K	≥90	112 lm/W	4,200 lm
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	4000 K	≥90	125 lm/W	4,200 lm
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	4000 K	≥90	120 lm/W	3,600 lm
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	4000 K	≥90	124 lm/W	3,600 lm
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	4000 K	≥90	96 lm/W	3,600 lm
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	4000 K	≥90	95.5 lm/W	4,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	4000 K	≥90	94.5 lm/W	4,200 lm
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	4000 K	≥90	124 lm/W	3,600 lm
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	4000 K	≥90	124 lm/W	3,600 lm
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	4000 K	≥90	122 lm/W	3,600 lm
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	4000 K	≥90	141 lm/W	3,600 lm
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	4000 K	≥90	125 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	4000 K	≥90	124 lm/W	4,200 lm
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	4000 K	≥90	120 lm/W	3,600 lm
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	4000 K	≥90	88 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	4000 K	≥90	86.5 lm/W	3,600 lm
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	4000 K	≥90	124 lm/W	3,600 lm
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	4000 K	≥90	96 lm/W	3,600 lm
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	4000 K	≥90	94.5 lm/W	4,200 lm
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	4000 K	≥90	94.5 lm/W	4,200 lm
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	4000 K	≥90	95.5 lm/W	4,200 lm
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	4000 K	≥90	96 lm/W	3,600 lm
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	4000 K	≥90	97.5 lm/W	3,600 lm
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	4000 K	≥90	142 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	4000 K	≥90	140 lm/W	4,200 lm
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	3000 K	≥90	136 lm/W	4,200 lm
10429700	RC340B LED36S/940 PSD	4000 K	90	144 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W60L60 PCV PCS PIP				
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	4000 K	≥90	96 lm/W	3,600 lm
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	4000 K	≥90	144 lm/W	3,600 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	37.5 W
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	37 W
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	44 W
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	44.5 W
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	41 W
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	41.5 W
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	48 W
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	49 W
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	37.5 W
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	44.5 W
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	37 W
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	37 W
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	37 W
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	44.5 W
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	44.5 W
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	47.5 W
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	47.5 W
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	30 W
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	30 W
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	31 W
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	32.5 W
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	33 W
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	33 W
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	33.5 W
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	37 W
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	37.5 W
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	33.5 W

Order Code	Full Product Name	Power Consumption
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	30 W
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	29 W
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	47.5 W
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	44.5 W
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	30 W
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	31 W
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	37.5 W
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	44 W
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	44.5 W
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	31 W
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	29 W
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	37 W
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	29 W
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	29.5 W
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	25.5 W
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	30 W
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	30 W
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	33.5 W
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	34 W
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	31 W
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	30 W
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	25 W
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	25 W
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	30 W

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	30 W
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	30 W
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	37 W
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	41 W
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	41.5 W
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	29 W
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	37.5 W
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	44.5 W
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	44.5 W
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	47.5 W
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	44.5 W
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	44 W

Order Code	Full Product Name	Power Consumption
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	37 W
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	29.5 W
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	47.5 W
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	44.5 W
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	30 W
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	31 W
10429700	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	25 W
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	37 W
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	37 W
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	25 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	No
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	No
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	No
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	No
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	No
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	Yes
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	Yes
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	Yes
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	Yes
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	Yes
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	Yes
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	Yes
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	No
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	No
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	No
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	No
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	Yes
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	Yes
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	Yes
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	Yes

Order Code	Full Product Name	Dimmable
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	No
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	No
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	Yes
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	No
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	No
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	No
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	Yes
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	Yes
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	No
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	No
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	No
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	No
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	No
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	Yes
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	Yes
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	No

FlexBlend Recessed

Order Code	Full Product Name	Dimmable
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	Yes
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	Yes
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	Yes
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	Yes

Order Code	Full Product Name	Dimmable
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	Yes
10429700	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	Yes
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes

Approval and Application

Order Code	Full Product Name	Ingress protection code
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	IP20
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	IP20
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	IP20
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	IP20
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	IP20
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	IP20
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	IP20
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	IP20
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	IP20
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	IP20
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	IP20
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	IP20
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	IP20
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	IP20
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	IP20
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	IP20
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	IP20
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	IP54
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	IP54
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	IP54
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	IP54
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	IP54
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	IP54
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	IP54
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	IP54
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	IP54
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	IP54
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	IP54
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	IP54
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	IP20
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	IP20
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	IP20
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	IP54
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	IP54
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	IP20
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	IP20
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	IP20
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	IP54
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	IP54
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	IP54

Order Code	Full Product Name	Ingress protection code
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	IP54
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	IP20
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	IP54
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	IP54
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	IP54
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	IP54
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	IP54
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	IP54
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	IP54
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	IP54
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	IP54
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	IP54
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	IP54
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	IP54
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	IP54
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	IP54
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	IP54
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	IP54
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	IP20
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	IP20
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	IP20
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	IP54
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	IP20
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	IP20
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	IP20
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	IP20
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	IP20
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	IP20
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	IP20
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	IP20
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	IP20
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	IP54
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	IP20
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	IP20
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	IP54
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	IP54
10429700	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	IP54
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	IP20
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	IP20
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	IP20

FlexBlend Recessed

Order Code	Full Product Name	Ingress protection code
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	IP54

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	(0.38, 0.37) SDCM <3
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	(0.38, 0.37) SDCM <3
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	(0.38, 0.37) SDCM <3
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	(0.38, 0.37) SDCM <3
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	(0.38, 0.37) SDCM <3
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	(0.43, 0.40) SDCM <3
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	(0.43, 0.40) SDCM <3
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	(0.38, 0.37) SDCM <3
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	(0.38, 0.37) SDCM <3
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	(0.43, 0.40) SDCM <3
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	(0.38, 0.37) SDCM <3
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	(0.38, 0.37) SDCM <3
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	(0.38, 0.37) SDCM <3
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	(0.43, 0.40) SDCM <3
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	(0.38, 0.37) SDCM <3
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	(0.38, 0.37) SDCM <3
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	(0.43, 0.40) SDCM <3
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	(0.43, 0.40) SDCM <3
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3

Order Code	Full Product Name	Initial chromaticity
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	(0.38, 0.37) SDCM <3
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	(0.43, 0.40) SDCM <3
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	(0.38, 0.37) SDCM <3
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	(0.38, 0.37) SDCM <3
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	(0.38, 0.37) SDCM <3
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	(0.38, 0.37) SDCM <3
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	(0.38, 0.37) SDCM <3
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	(0.38, 0.37) SDCM <3
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	(0.38, 0.37) SDCM <3
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	(0.43, 0.40) SDCM <3
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	(0.38, 0.37) SDCM <3
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	(0.38, 0.37) SDCM <3
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	(0.38, 0.37) SDCM <3
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	(0.43, 0.40) SDCM <3
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	(0.38, 0.37) SDCM <3
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	(0.38, 0.37) SDCM <3
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	(0.43, 0.40) SDCM <3
10429700	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	(0.38, 0.37) SDCM <3
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	(0.38, 0.37) SDCM <3
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	(0.38, 0.37) SDCM <3
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	(0.38, 0.37) SDCM <3

Over Time Performance (IEC Compliant)

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	0.01 %
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	0.01 %
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	0.01 %
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	0.01 %
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	0.01 %
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	0.01 %
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	0.01 %
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	0.01 %
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	0.01 %
10292700	RC340B LED42S/940 PSD W30L120 VPC MLO W	0.01 %
10293400	RC340B LED42S/940 PSD W30L120 CPC MLO W	0.01 %
10294100	RC340B LED42S/930 PSD W30L120 VPC MLO W	0.01 %
10295800	RC340B LED42S/930 PSD W30L120 CPC MLO W	0.01 %
10300900	RC340B LED42S/940 PSD W30L120 VPC PCS W	0.01 %
10301600	RC340B LED42S/940 PSD W30L120 CPC PCS W	0.01 %
10304700	RC340B LED42S/930 PSD W30L120 VPC PCS W	0.01 %
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	0.01 %
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	0.01 %
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	0.01 %
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	0.01 %
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	0.01 %
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	0.01 %
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	0.01 %
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	0.01 %
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	0.01 %
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
10285900	RC340B LED42S/930 PSD W60L60 CPC MLO W	0.01 %
10290300	RC340B LED42S/940 PSD W60L60 CPC MLO W	0.01 %
10298900	RC340B LED42S/940 PSD W60L60 CPC PCS W	0.01 %
10302300	RC340B LED42S/930 PSD W60L60 CPC PCS W	0.01 %
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	0.01 %
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	0.01 %
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	0.01 %
10330600	RC340B LED42S/930 PSD W30L120 CPC PCS W	0.01 %
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	0.01 %
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	0.01 %
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	0.01 %
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	0.01 %
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	0.01 %
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	0.01 %
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	0.01 %
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	0.01 %
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	0.01 %
10296500	RC340B LED42S/930 PSD W60L60 VPC PCS W	0.01 %
10297200	RC340B LED42S/940 PSD W60L60 VPC PCS W	0.01 %
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	0.01 %
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	0.01 %
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	0.01 %
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	0.01 %
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	0.01 %
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	0.01 %
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	0.01 %
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	0.01 %
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	0.01 %
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	0.01 %
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	0.01 %
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	0.01 %
10275000	RC340B LED42S/930 PSD W60L60 VPC MLO W	0.01 %
10289700	RC340B LED42S/940 PSD W60L60 VPC MLO W	0.01 %
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	0.01 %
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	0.01 %
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	0.01 %
10287300	RC340B LED42S/930 PSD W60L60 PCV MLO W	0.01 %
10291000	RC340B LED42S/940 PSD W60L60 PCV MLO W	0.01 %
10299600	RC340B LED42S/940 PSD W60L60 PCV PCS W	0.01 %
10303000	RC340B LED42S/930 PSD W60L60 PCV PCS W	0.01 %
10429700	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	-
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	0.01 %
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	0.01 %
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	-

FlexBlend Recessed

