



VersaForm - Clean harmonious style and superior performance in a seamless upgradable design.

VersaForm

Specifically designed to blend high performance LED technology with versatile options to suit any area, VersaForm allows you to enjoy the latest LED energy efficiencies in concert with your unique style, and as your needs evolve, it's simple to change or upgrade with our unique detachable light engine.

Benefits

- Wide palette of sizes, lumen packages, color temperatures, color renderings, housings
- Optional controls and sensors
- Simple to change or upgrade with unique detachable light engine

Features

- Multiple lumen packages, color temperatures and color renderings
- Upgradable LED light engine without expensive rewiring or total fixture replacement
- Available in 1'x4', 2'x2' & 2'x4', Recessed and surface versions
- Fixtures can be fastened directly to the T-bar grid and/or tied-off to the building structure
- Optional drywall kits available

VersaForm

Application

- Office
- Banks
- Hospitality
- Fashion

Versions

