



# FluxStream – simple, easy, convenient

## FluxStream LED Strip

The FluxStream family of LED linear luminaires deliver high-quality, more uniform light versus fluorescents for a greater range of applications. Choose FluxStream for simple, robust LED light industrial commercial linear lighting solutions that need to perform and endure.

### Benefits

- Simple form
- Convenient specification
- Ease of installation
- Ease of maintenance

### Features

- Delivers up to 133 LPW
- Multiple CCT and lumen options
- Standard 0-10V dimming
- Multiple mounting methods

### Application

- Office
- Banks
- Hospitality
- Manufacturing
- Education

# FluxStream LED Strip

## Versions



FSS220L840-UNV-DIM



FSS330L840-UNV-DIM



FSS440L840-UNV-DIM



FSS8110L840-UNV-DIM



FSS880L840-347-DIM

