



Combines style and performance

SofTrace Recessed LED

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Benefits

- Achieve energy efficiency targets and reduce energy-related costs
- Excellent aesthetics and light distribution
- Ease of maintenance

Features

- Reliable performance up to 130 LPW
- Optional occupancy and daylighting sensors
- Standard 0-10V dimming
- Uniform, glare free light distribution

Application

- Office
- Hospitality
- Education

SofTrace Recessed LED

Versions

