



Creativity and continuity can coexist

PureForm LED area medium P26

Gardco PureForm site and area medium LED features a sleek, low profile design and optimal performance. PureForm site and area medium is designed to achieve maximum pole spacing, with lumen output up to 28,000 lumens. Multiple distribution and shielding options are available to achieve maximum control. A full range of control options provide additional energy savings.

Benefits

- Sleek, low profile design blends in with architecture.
- Both comfort optics and precision optics available, suitable for a range of mounting heights and lumen output.
- Seamless integration with the latest controls solutions makes management easy, further enhancing value.

Features

- Standard arm, wall bracket, adjustable slitter, and retrofit arm mount available
- Precision optics designed for optimal spacing and performance
- Type 2, 3, 4, 5, 5W, AFR and BLC optical distributions
- A full range of control options provide additional energy savings

PureForm LED area medium P26

Application

- Education
- Municipal Buildings
- Parks and Plazas
- Walkways
- Office
- Hospitality
- Education
- Municipal Buildings
- Parks and Plazas
- Walkways
- Office
- Hospitality

