



# CUL2 – offering a distinctive appearance to any outdoor landscape

## CUL2 Path Light

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Sources include standard low voltage lamps and LED that offers 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80.

### Benefits

- Natural aging color
- Easy hookup to the low voltage supply cable
- Easy installation and maintenance
- Dust tight and sealed against direct jets of water
- Offers 50,000 hour life with LED

### Features

- Solid copper housing
- Pre-wired
- Ships with S7 mounting stake
- IP67 rated
- Available with conventional and LED technology

### Application

- Walkways

## CUL2 Path Light

### Versions

