



Dusk to Dawn LED - value-focused, quality illumination and efficiency

Dusk to Dawn Area LED Gen-2

The Dusk to Dawn LED Luminaire Gen 2 offers an economical solution with enhanced generation chip on board LED performance for general purpose area and security lighting. The luminaire can be direct mounted to vertical surfaces or mounted onto 1 1/2" O.D. arms. Arm is also available as an accessory ordered separately. A 120V NEMA twist lock photo cell is included as standard. This versatile luminaire easily retrofits onto existing arms and offers one of the most affordable and efficient energy saving solutions available.

Benefits

- Up to 70% energy savings over 100W metal halide sources
- Long LED life
- Maximizes efficiency
- Quick and easy installation

Features

- Uses chip-on-board LED technology
- One-piece die cast aluminum housing with integral arm mounting hub
- Durable polycarbonate lens system utilizes a refractive prism design
- Specular aluminum reflector
- NEMA twist lock photo cell

Application

- Security Lighting