



# Design, Efficiency, and Flexibility

## Calculite CFL 7"

Calculite open wall wash downlights provide wide, uniform wall washing together with roomside downlighting. Downlight contribution matches companion Downlight in distribution. Also effective for lighting shelving or displays.

### Benefits

- Reflector: 16 ga. Alzak® aluminum, 50° visual cutoff to lamp and lamp image, medium distribution
- Stamped steel frames suitable for dry or wet plaster ceilings up to 1 1/8" thick

### Features

- Precision-tooled steel friction springs secure reflector to mounting frame for quick, tool-less installation
- Socket Cup snaps onto reflector neck to assure consistently correct optical alignment without tools

### Application

- Office
- Banks
- Hospitality
- Airports
- Fashion
- Hospitals and Care Centers
- Education

## Calculite CFL 7"

### Versions

