



Consistent visual comfort

Evolution MR16 4"

Recessed adjustable downlights provide accent and task lighting or downlighting in sloped ceilings using low voltage MR-16 lamps available in a wide variety of wattages and beam spreads. 2" aperture pinhole reflector (C4MR2) match other Evolution downlights.

Benefits

- 50° physical and reflected cut off
- Precision optics minimize aperture brightness
- Unitized optics ensure consistent performance

Features

- Perimeter frosted lens for smooth, even beam
- Locking vertical and horizontal adjustment
- Matte black shield blocks view into fixture

Application

- Residential
- Office
- Banks
- Hospitality
- Airports
- Fashion

Evolution MR16 4"

Versions

