



**Ideal general purpose
downlight solution,
providing comfortable
quality light. Available in
new construction and
remodeler frame with
interchangeable light
engine that is offered in
two lumen packages.**

LyteCaster LED Downlight

Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

Benefits

- Comprehensive low cost IC family provides great value and visual performance

LyteCaster LED Downlight

Features

- 4,5,6" round and square
- Efficacy up to 90lm/W
- Lumens: 650-2000
- Wattage: 7-20W
- Voltage: 120V or 120V-277V

Application

- Residential
- Hospitality

Versions

