



Create efficiency in your design

LyteProfile LED

LyteProfile LED downlights are designed for new construction and include downlight and wall wash distributions. They are highly energy efficient with up to 100 lm/w, provide a full 60 degree cutoff, and feature an impressively shallow 4.5" housing.

Benefits

- Fixture depth remains below 4 1/2" deep and allows for a consistent 2" ceiling depth
- Innovative mid-flux LED design eliminates pixelation and provides smooth, even illumination with simplified thermal management
- The product line delivers up to 90 lm/W at the emitted luminaire level while providing a comfortable 60° cut-off to both the actual and reflected source

Features

- Cutting edge technology employs the latest in thermal management and significantly reduces the size and physical material employed in the luminaire
- Designed to meet standard commercial lighting requirements with choices of 1000 lm, 1500 lm downlight or lensed wall wash in either a 4" or 6" apertures
- and up to 2000 lm in the 6" aperture
- Three component system design enables easy servicing plus upgradeability

Application

- Office
- Banks
- Hospitality
- Airports
- Fashion

LyteProfile LED

Versions

