



Designed to enhance

Optima LED post top (OT10-OT20)

The Lumec Optima LED post top luminaires are the perfect choice for urban projects such as streets, walkways and public spaces that compel that extra little bit of detail. This timeless luminaire is made from top-quality materials, is easy to maintain, and adds a distinctive decorative aspect to any contemporary environment. Paired with the latest LED technology, its IP66 rating, multiple lumen outputs, various luminaire style options and energy-saving control options are well suited to meet wide range of project requirements

Benefits

- Versatile luminaires available with various style options
- Post top and pendant versions available to suit a wide range of applications
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance
- Maximizes energy savings with multiple driver options and programmed dimming options

Features

- Multiple lumen packages with output of up to 7,853 lumens
- Type 2, 3, 4, and 5 optics available
- 4000K and 3000K color temperatures available
- Dimming driver standard

Application

- Municipal Buildings
- Parks and Plazas
- Road and Street

Optima LED post top (OT10-OT20)

Versions

