



# The new generation of universal T8 LEDtube lighting

## CorePro LED tube Universal T8

The new Philips CorePro LEDtube Universal T8 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips CorePro LEDtube Universal T8 directly fits in luminaires operating either on Electro Magnetic ballasts or HF Electronic ballasts or mains power connection. So simple to operate and no need to carry double stock of products! Perfectly safe, reliable & easy to install Philips CorePro LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to save energy and lower investment.

### Benefits

- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to longer lifetime than conventional lamps
- Fastest and easiest way to upgrade existing luminaires to LEDtechnology; completely safe product and installation process

### Features

- Replacement of existing T8 lamps on both EM/HF ballast and mains power connection installation
- Energy savings compared with fluorescent tubes
- InstantFit technology for largest ballast compatibility
- No mercury

### Application

- Offices, shops, classrooms


# CorePro LED tube Universal T8

## Versions



LEDtube G13

## Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube UN 1500mm HO 23W865 T8	27.9 mm	28 mm	1500 mm	1505.9 mm	1514.2 mm
CorePro LEDtube UN 1500mm HO 23W830 T8	27.9 mm	28 mm	1500 mm	1505.9 mm	1514.2 mm
CorePro LEDtube UN 1200mm HO 18W840 T8	27.9 mm	28 mm	1199.4 mm	1205.3 mm	1213.6 mm
CorePro LEDtube UN 1200mm HO 18W865 T8	27.9 mm	28 mm	1199.4 mm	1205.3 mm	1213.6 mm
CorePro LEDtube UN 1500mm HO 23W840 T8	27.9 mm	28 mm	1500 mm	1505.9 mm	1514.2 mm
CorePro LEDtube UN 1200mm HO 18W830 T8	27.9 mm	28 mm	1199.4 mm	1205.3 mm	1213.6 mm

# CorePro LED tube Universal T8

## Approval and Application

Energy Efficiency Label (EEL) A+

## Controls and Dimming

Dimmable No

## Operating and Electrical

Input Frequency 50 to 60 Hz

Voltage (Nom) 220-240 V

Starting Time (Nom) 0.5 s

## General Information

Cap-Base G13

Nominal Lifetime (Nom) 30000 h

Rated Lifetime (Hours) 30000 h

Switching Cycle 50000X

## Light Technical

Beam Angle (Nom) 240 °

Color Rendering Index (Nom) 80

Llmf At End Of Nominal Lifetime (Nom) 70 %

Rated Beam Angle 240 °

## Temperature

T-Ambient (Max) 45 °C

T-Ambient (Min) -20 °C

T-Case Maximum (Nom) 65 °C

T-Storage (Max) 65 °C

T-Storage (Min) -40 °C

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
80166600	CorePro LEDtube UN 1200mm HO 18W830 T8	18 kWh
80168000	CorePro LEDtube UN 1200mm HO 18W840 T8	18 kWh
80170300	CorePro LEDtube UN 1200mm HO 18W865 T8	18 kWh
80172700	CorePro LEDtube UN 1500mm HO 23W830 T8	23 kWh
80174100	CorePro LEDtube UN 1500mm HO 23W840 T8	23 kWh
80176500	CorePro LEDtube UN 1500mm HO 23W865 T8	23 kWh

## Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
80166600	CorePro LEDtube UN 1200mm HO 18W830 T8	18 W
80168000	CorePro LEDtube UN 1200mm HO 18W840 T8	18 W
80170300	CorePro LEDtube UN 1200mm HO 18W865 T8	18 W

Order Code	Full Product Name	Power (Rated) (Nom)
80172700	CorePro LEDtube UN 1500mm HO 23W830 T8	23 W
80174100	CorePro LEDtube UN 1500mm HO 23W840 T8	23 W
80176500	CorePro LEDtube UN 1500mm HO 23W865 T8	23 W

## Light Technical

Order Code	Full Product Name	Color Code	Correlated		Luminous Flux (Rated) (Nom)
			Color Temperature (Nom)	Luminous Flux (Nom)	
80166600	CorePro LEDtube UN 1200mm HO 18W830 T8	830	3000 K	1850 lm	1850 lm
80168000	CorePro LEDtube UN 1200mm HO 18W840 T8	840	4000 K	2000 lm	2000 lm

Order Code	Full Product Name	Color Code	Correlated		Luminous Flux (Rated) (Nom)
			Color Temperature (Nom)	Luminous Flux (Nom)	
80170300	CorePro LEDtube UN 1200mm HO 18W865 T8	865	6500 K	2000 lm	2000 lm
80172700	CorePro LEDtube UN 1500mm HO 23W830 T8	830	3000 K	2500 lm	2500 lm

# CorePro LED tube Universal T8

Order Code	Full Product Name	Color Code	Correlated Color		Luminous Flux (Nom)	Luminous Flux (Rated)
			Temperature (Nom)			
80174100	CorePro LEDtube UN 1500mm HO 23W840 T8	840	4000 K		2700 lm	2700 lm
80176500	CorePro LEDtube UN 1500mm HO 23W865 T8	865	6500 K		2700 lm	2700 lm

