



A high-resolution exterior linear direct-view luminaire with intelligent RGBW light

iColor Accent Compact, RGBW

iColor Accent Compact, RGBW is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact, RGBW adds a separate white LED, creating better-quality whites compared to RGB. iColor Accent Compact, RGBW accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact, RGBW: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Benefits

- One luminaire, multiple applications – Create media facades or architectural outlines and enhancements
- Highest resolution in a direct-view linear product
- ActiveSite enabled for remote management – enjoy peace of mind and enhance your brand image

Features

- Small size & end-end connections for accent/effect lighting and low-resolution video grids
- The low-voltage system with remote power supplies eases long-term maintenance
- Direct Ethernet data input for video frame rate displays

iColor Accent Compact, RGBW

Application

- Architectural accent and effect lighting

Versions



Product details



iColor Accent Compact Clear Input
Detail Shot



iColor Accent Compact Clear Input
Detail Photo

iColor Accent Compact, RGBW

