



Extended product family – to cover large-scale ceilings with 600x1,200 versions

SmartBright Slim Panel – Extension

SmartBright Slim Panel provides the most affordable LED solution to replace the TL troffer. Based on the standard version, we have extended the product family to 600x1,200 versions. With its edge-light architecture, the SmartBright Slim Panel will deliver comfortable light with excellent uniformity.

Benefits

- Slim design with edge-lit architecture
- Full window illumination delivers comfortable light with excellent uniformity
- Easy to install with the driver fixed on the luminaire

Features

- System efficacy 80 lm/W,
- High reliability, 30 k hours (L70@25deg)
- CRI > 80, SDCM 5

Application

- Open office
- Meeting room
- Hospital
- Library
- Circulation area

SmartBright Slim Panel – Extension

Versions



Product details



SmartBright Slim Panel – Extension

Application Conditions

Ambient temperature range	-10 to +35 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Beam angle of light source	120 °
Protection class IEC	Safety class II (II)
Optical cover/lens type	Polystyrene bowl/ cover prismatic
Driver included	Yes
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	Symmetrical

Initial Performance (IEC Compliant)

Initial chromaticity	≤5
Init. Colour Rendering Index	>80
Initial LED luminaire efficacy	80 lm/W
Initial luminous flux	5000 lm
Luminous flux tolerance	+/-10%
Initial input power	62 W

Mechanical and Housing

Colour	White
--------	-------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature
911401719272	RC091V LED50S/840 PSU W60L120 ANZ	4000 K
911401719282	RC091V LED50S/865 PSU W60L120 ANZ	6500 K

