



TruGroove recessed micro – Seamless 1.75" ribbon of light with exceptional performance and versatility for functional and decorative applications.

TruGroove recessed micro

TruGroove recessed micro delivers the perfect combination of slender aesthetic and lighting control, creating luminous environments with exceptional uniformity and wide row spacing from a 1.75" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Benefits

- Elevated performance to a whole new level in narrow aperture lighting
- Wide row spacing with fewer fixtures and lower energy consumption
- Ideal for a variety of applications

TruGroove recessed micro

Features

- MesoOptics DX delivers an optimal batwing distribution
- Available in both symmetric, and asymmetric throws
- Integrated Interact Pro scalable wireless sensors
- Multiple lumen package, color temperature and CRI options
- Continuous lines of uninterrupted luminance to 1/8"

Application

- Office
- Healthcare
- Education
- Retail
- Hospitality
- Airport

Versions

