



GentleSpace gen3: adaptable high-bay lighting offering high efficiency and connectivity options to lighting systems and software applications.

GentleSpace Gen3

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based system and software applications such as Interact Industry. Overall, whether you are looking for a reliable “fit & forget” solution or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

GentleSpace Gen3

Benefits

- High quality visibility combined with great uniformity and reduced glare
- Robust and reliable solution for long service life
- Highly efficient solution, offering an attractive total cost of ownership
- Flexibility enabled by high degree of adaptability to changing application needs
- Ready to be connected to existing and upcoming system and software applications
- Extensive application coverage including food production, manufacturing different high ceiling, hall application

Features

- High efficiency of up to 155 lm/W
- Long service life of L80 at 100K hrs
- Detachable mounting system for ease of installation
- Fully compliant with EN-12464-1; low glare rating and color rendering of ≥ 80
- Option for dust cover to meet requirements of the food industry
- Suitable for new builds or point-for-point replacement of HPI 250W, HPL 400W or HPI 400W, reducing energy consumption by up to 65%
- Wide variety of optics to meet application requirements, also with the option of adjustable optics variant with the flexibility to shift from NB to WB with easy adjustment mechanism
- Interact Industry and Philips GreenWarehouse ready

Application

- Food production and manufacturing
- Warehouses and logistics centers
- Indoor sports halls, swimming pools, and exhibition halls

Versions



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Wide beam - Silver



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Wide beam - Silver



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Medium beam - Silver



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Medium beam - Silver

GentleSpace Gen3

Versions



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - High-rack optic - Silver



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Medium beam - White



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Wide beam - White



New Highbay - 840 neutral white -
Power supply unit with DALI
interface - Wide beam - Silver



New Highbay - - - 840 neutral
white - Power supply unit with
DALI interface - Wide beam -
Polymethyl methacrylate bowl/
cover - Silver

Application Conditions

Ambient temperature range	-30 to +45 °C
Maximum dim level	10%

Approval and Application

Ingress protection code	IP65
-------------------------	------

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

Beam angle of light source	114 °
CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
Light source replaceable	Yes
Number of gear units	1 unit

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	≥80
Luminous flux tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L90B50	50000 h
---------------------------	---------

Application Conditions

Order Code	Full Product Name	Suitable for random switching
910500465536	BY481P LED250S/840 PSD WB GC SI	No
910500465537	BY481P LED250S/840 PSD MB GC SI	No
910500465538	BY481P LED350S/840 PSD MB GC SI	No
910500465540	BY481P LED250S/840 PSD NB GC SI	No
910500465547	BY481P LED250S/840 PSD WB PC SI	No
910500465549	BY481P LED350S/840 PSD WB GC SI	No
910500465550	BY481P LED250S/840 PSD MB PC SI	No
910500465569	BY481P LED250S/840 PSD HRO GC SI	No
910500465573	BY481P LED350S/840 PSD HRO GC SI	No
910500465574	BY481P LED350S/840 PSD NB GC SI	No
910500465575	BY481P LED250S/840 PSD HRO PC SI	No
910500465599	BY481P LED350S/840 PSD WB PC SI	No
910500465602	BY481P LED250S/840 PSD NB PC SI	No
910500465605	BY481P LED350S/840 PSD MB PC SI	No
910500465606	BY481P LED350S/840 PSD HRO PC SI	No
910500465539	BY480P LED130S/840 PSD WB GC SI	No
910500465542	BY480P LED170S/840 PSD WB GC SI	No
910500465544	BY480P LED130S/840 PSD MB GC SI	No
910500465545	BY480P LED170S/840 PSD HRO GC SI	No
910500465548	BY480P LED130S/840 PSD HRO GC SI	No
910500465551	BY480P LED170S/840 PSD MB GC SI	No
910500465568	BY480P LED130S/840 PSD WB PC SI	No
910500465579	BY480P LED170S/840 PSD NB GC SI	No
910500465580	BY480P LED170S/840 PSD WB PC SI	No
910500465589	BY480P LED130S/840 PSD NB PC SI	No
910500465591	BY480P LED130S/840 PSD NB GC SI	No
910500465593	BY480P LED130S/840 PSD HRO PC SI	No
910500465595	BY480P LED170S/840 PSD MB PC SI	No
910500465597	BY480P LED130S/840 PSD MB PC SI	No
910500465603	BY480P LED170S/840 PSD HRO PC SI	No
910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	Yes
910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	Yes
910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	Yes
910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	Yes
910500465556	BY481P LED250S/840 PSD MB GC SI BR	No
910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	Yes
910500465564	BY481P LED250S/840 PSD WB GC SI BR	No
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	Yes
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	Yes
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	Yes
910500465584	BY481P LED250S/840 PSD NB GC SI BR	No
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	No
910500465596	BY481P LED350S/840 PSD MB GC SI BR	No
910500465608	BY481P LED350S/840 PSD WB GC SI BR	No
910500465546	BY480P LED170S/840 PSD MB GC WH BR	No
910500465570	BY480P LED170S/840 PSD WB GC WH BR	No
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	Yes
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	Yes
910500465558	BY480P LED170S/840 PSD WB GC SI BR	No
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	Yes
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	Yes

Order Code	Full Product Name	Suitable for random switching
910500465561	BY480P LED130S/840 PSD MB GC SI BR	No
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	Yes
910500465572	BY480P LED130S/840 PSD WB GC SI BR	No
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	Yes
910500465585	BY480P LED170S/840 PSD MB GC SI BR	No
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	No
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	Yes
910500465604	BY480P LED170S/840 PSD NB GC SI BR	No
910500465563	BY481P LED250S/840 PSD MB GC WH	No
910500465577	BY481P LED250S/840 PSD MB PC WH	No
910500465583	BY481P LED250S/840 PSD WB GC WH	No
910500465607	BY481P LED250S/840 PSD HRO GC WH	No
910500465566	BY480P LED130S/840 PSD WB GC WH	No
910500465578	BY480P LED170S/840 PSD MB GC WH	No
910500465581	BY480P LED170S/840 PSD WB GC WH	No
910500465582	BY480P LED130S/840 PSD MB GC WH	No
910500465586	BY480P LED170S/840 PSD HRO GC WH	No
910500465588	BY480P LED170S/840 PSD NB GC WH	No
910500465609	BY480P LED170S/840 PSD WB PC WH	No
910500465587	BY481P LED250S/840 PSD MB GC WH BR	No
910500465594	BY481P LED250S/840 PSD WB GC WH BR	No
910500465801	BY480P LED130S/840 PSD NBA GC SI	No
910500465802	BY480P LED170S/840 PSD NBA GC SI	No
910500465803	BY481P LED250S/840 PSD NBA GC SI	No
910500465804	BY481P LED350S/840 PSD NBA GC SI	No
910500465805	BY481P LED350S/840 PSD NBA PC SI	No
910500465806	BY481P LED250S/840 PSD NBA PC SI	No
910500465807	BY480P LED130S/840 PSD NBA PC SI	No
910500465808	BY480P LED170S/840 PSD NBA PC SI	No

Approval and Application

Order Code	Full Product Name	Mech. impact protection code	Order Code	Full Product Name	Mech. impact protection code
910500465536	BY481P LED250S/840 PSD WB GC SI	IK07	910500465545	BY480P LED170S/840 PSD HRO GC SI	IK07
910500465537	BY481P LED250S/840 PSD MB GC SI	IK07	910500465548	BY480P LED130S/840 PSD HRO GC SI	IK07
910500465538	BY481P LED350S/840 PSD MB GC SI	IK07	910500465551	BY480P LED170S/840 PSD MB GC SI	IK07
910500465540	BY481P LED250S/840 PSD NB GC SI	IK07	910500465568	BY480P LED130S/840 PSD WB PC SI	IK08
910500465547	BY481P LED250S/840 PSD WB PC SI	IK08	910500465579	BY480P LED170S/840 PSD NB GC SI	IK07
910500465549	BY481P LED350S/840 PSD WB GC SI	IK07	910500465580	BY480P LED170S/840 PSD WB PC SI	IK08
910500465550	BY481P LED250S/840 PSD MB PC SI	IK08	910500465589	BY480P LED130S/840 PSD NB PC SI	IK08
910500465569	BY481P LED250S/840 PSD HRO GC SI	IK07	910500465591	BY480P LED130S/840 PSD NB GC SI	IK07
910500465573	BY481P LED350S/840 PSD HRO GC SI	IK07	910500465593	BY480P LED130S/840 PSD HRO PC SI	IK08
910500465574	BY481P LED350S/840 PSD NB GC SI	IK07	910500465595	BY480P LED170S/840 PSD MB PC SI	IK08
910500465575	BY481P LED250S/840 PSD HRO PC SI	IK08	910500465597	BY480P LED130S/840 PSD MB PC SI	IK08
910500465599	BY481P LED350S/840 PSD WB PC SI	IK08	910500465603	BY480P LED170S/840 PSD HRO PC SI	IK08
910500465602	BY481P LED250S/840 PSD NB PC SI	IK08	910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	IK07
910500465605	BY481P LED350S/840 PSD MB PC SI	IK08	910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	IK07
910500465606	BY481P LED350S/840 PSD HRO PC SI	IK08	910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	IK07
910500465539	BY480P LED130S/840 PSD WB GC SI	IK07	910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	IK07
910500465542	BY480P LED170S/840 PSD WB GC SI	IK07	910500465556	BY481P LED250S/840 PSD MB GC SI BR	IK07
910500465544	BY480P LED130S/840 PSD MB GC SI	IK07	910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	IK07

Order Code	Full Product Name	Mech. impact protection code
910500465564	BY481P LED250S/840 PSD WB GC SI BR	IK07
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	IK07
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	IK07
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	IK07
910500465584	BY481P LED250S/840 PSD NB GC SI BR	IK07
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	IK07
910500465596	BY481P LED350S/840 PSD MB GC SI BR	IK07
910500465608	BY481P LED350S/840 PSD WB GC SI BR	IK07
910500465546	BY480P LED170S/840 PSD MB GC WH BR	IK07
910500465570	BY480P LED170S/840 PSD WB GC WH BR	IK07
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	IK07
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	IK07
910500465558	BY480P LED170S/840 PSD WB GC SI BR	IK07
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	IK07
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	IK07
910500465561	BY480P LED130S/840 PSD MB GC SI BR	IK07
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	IK07
910500465572	BY480P LED130S/840 PSD WB GC SI BR	IK07
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	IK07
910500465585	BY480P LED170S/840 PSD MB GC SI BR	IK07
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	IK07
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	IK07

Order Code	Full Product Name	Mech. impact protection code
910500465604	BY480P LED170S/840 PSD NB GC SI BR	IK07
910500465563	BY481P LED250S/840 PSD MB GC WH	IK07
910500465577	BY481P LED250S/840 PSD MB PC WH	IK08
910500465583	BY481P LED250S/840 PSD WB GC WH	IK07
910500465607	BY481P LED250S/840 PSD HRO GC WH	IK07
910500465566	BY480P LED130S/840 PSD WB GC WH	IK07
910500465578	BY480P LED170S/840 PSD MB GC WH	IK07
910500465581	BY480P LED170S/840 PSD WB GC WH	IK07
910500465582	BY480P LED130S/840 PSD MB GC WH	IK07
910500465586	BY480P LED170S/840 PSD HRO GC WH	IK07
910500465588	BY480P LED170S/840 PSD NB GC WH	IK07
910500465609	BY480P LED170S/840 PSD WB PC WH	IK08
910500465587	BY481P LED250S/840 PSD MB GC WH BR	IK07
910500465594	BY481P LED250S/840 PSD WB GC WH BR	IK07
910500465801	BY480P LED130S/840 PSD NBA GC SI	IK07
910500465802	BY480P LED170S/840 PSD NBA GC SI	IK07
910500465803	BY481P LED250S/840 PSD NBA GC SI	IK07
910500465804	BY481P LED350S/840 PSD NBA GC SI	IK07
910500465805	BY481P LED350S/840 PSD NBA PC SI	IK08
910500465806	BY481P LED250S/840 PSD NBA PC SI	IK08
910500465807	BY480P LED130S/840 PSD NBA PC SI	IK08
910500465808	BY480P LED170S/840 PSD NBA PC SI	IK08

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
910500465536	BY481P LED250S/840 PSD WB GC SI	-	-	-	Wide beam
910500465537	BY481P LED250S/840 PSD MB GC SI	-	-	-	Medium beam
910500465538	BY481P LED350S/840 PSD MB GC SI	-	-	-	Medium beam
910500465540	BY481P LED250S/840 PSD NB GC SI	-	-	-	Narrow beam
910500465547	BY481P LED250S/840 PSD WB PC SI	-	-	-	Wide beam
910500465549	BY481P LED350S/840 PSD WB GC SI	-	-	-	Wide beam
910500465550	BY481P LED250S/840 PSD MB PC SI	-	-	-	Medium beam
910500465569	BY481P LED250S/840 PSD HRO GC SI	-	-	-	High-rack optic
910500465573	BY481P LED350S/840 PSD HRO GC SI	-	-	-	High-rack optic
910500465574	BY481P LED350S/840 PSD NB GC SI	-	-	-	Narrow beam
910500465575	BY481P LED250S/840 PSD HRO PC SI	-	-	-	High-rack optic

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
910500465599	BY481P LED350S/840 PSD WB PC SI	-	-	-	Wide beam
910500465602	BY481P LED250S/840 PSD NB PC SI	-	-	-	Narrow beam
910500465605	BY481P LED350S/840 PSD MB PC SI	-	-	-	Medium beam
910500465606	BY481P LED350S/840 PSD HRO PC SI	-	-	-	High-rack optic
910500465539	BY480P LED130S/840 PSD WB GC SI	-	-	-	Wide beam
910500465542	BY480P LED170S/840 PSD WB GC SI	-	-	-	Medium beam
910500465544	BY480P LED130S/840 PSD MB GC SI	-	-	-	Medium beam
910500465545	BY480P LED170S/840 PSD HRO GC SI	-	-	-	High-rack optic
910500465548	BY480P LED130S/840 PSD HRO GC SI	-	-	-	High-rack optic
910500465551	BY480P LED170S/840 PSD MB GC SI	-	-	-	Medium beam
910500465568	BY480P LED130S/840 PSD WB PC SI	-	-	-	Wide beam

GentleSpace Gen3

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
910500465579	BY480P LED170S/840 PSD NB GC SI	-	-	-	Narrow beam
910500465580	BY480P LED170S/840 PSD WB PC SI	-	-	-	Wide beam
910500465589	BY480P LED130S/840 PSD NB PC SI	-	-	-	Narrow beam
910500465591	BY480P LED130S/840 PSD NB GC SI	-	-	-	Narrow beam
910500465593	BY480P LED130S/840 PSD HRO PC SI	-	-	-	High-rack optic
910500465595	BY480P LED170S/840 PSD MB PC SI	-	-	-	Medium beam
910500465597	BY480P LED130S/840 PSD MB PC SI	-	-	-	Medium beam
910500465603	BY480P LED170S/840 PSD HRO PC SI	-	-	-	High-rack optic
910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	-	-	-	Medium beam
910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	-	-	-	Wide beam
910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	-	-	-	High-rack optic
910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	-	-	-	Medium beam
910500465556	BY481P LED250S/840 PSD MB GC SI BR	-	-	-	Medium beam
910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	-	-	-	Wide beam
910500465564	BY481P LED250S/840 PSD WB GC SI BR	-	-	-	Wide beam
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	-	-	-	High-rack optic
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	-	-	-	Narrow beam
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	-	-	-	Narrow beam
910500465584	BY481P LED250S/840 PSD NB GC SI BR	-	-	-	Narrow beam
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	-	-	-	High-rack optic
910500465596	BY481P LED350S/840 PSD MB GC SI BR	-	-	-	Medium beam
910500465608	BY481P LED350S/840 PSD WB GC SI BR	-	-	-	Wide beam
910500465546	BY480P LED170S/840 PSD MB GC WH BR	-	-	-	Medium beam
910500465570	BY480P LED170S/840 PSD WB GC WH BR	-	-	-	Wide beam
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	-	-	-	High-rack optic

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	-	-	-	Wide beam
910500465558	BY480P LED170S/840 PSD WB GC SI BR	-	-	-	Wide beam
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	-	-	-	Medium beam
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	-	-	-	Wide beam
910500465561	BY480P LED130S/840 PSD MB GC SI BR	-	-	-	Medium beam
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	-	-	-	Medium beam
910500465572	BY480P LED130S/840 PSD WB GC SI BR	-	-	-	Wide beam
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	-	-	-	High-rack optic
910500465585	BY480P LED170S/840 PSD MB GC SI BR	-	-	-	Medium beam
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	-	-	-	High-rack optic
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	-	-	-	Narrow beam
910500465604	BY480P LED170S/840 PSD NB GC SI BR	-	-	-	Narrow beam
910500465563	BY481P LED250S/840 PSD MB GC WH	-	-	-	Medium beam
910500465577	BY481P LED250S/840 PSD MB PC WH	-	-	-	Medium beam
910500465583	BY481P LED250S/840 PSD WB GC WH	-	-	-	Wide beam
910500465607	BY481P LED250S/840 PSD HRO GC WH	-	-	-	High-rack optic
910500465566	BY480P LED130S/840 PSD WB GC WH	-	-	-	Wide beam
910500465578	BY480P LED170S/840 PSD MB GC WH	-	-	-	Medium beam
910500465581	BY480P LED170S/840 PSD WB GC WH	-	-	-	Wide beam
910500465582	BY480P LED130S/840 PSD MB GC WH	-	-	-	Medium beam
910500465586	BY480P LED170S/840 PSD HRO GC WH	-	-	-	High-rack optic
910500465588	BY480P LED170S/840 PSD NB GC WH	-	-	-	Narrow beam
910500465609	BY480P LED170S/840 PSD WB PC WH	-	-	-	Wide beam
910500465587	BY481P LED250S/840 PSD MB GC WH BR	-	-	-	Wide beam
910500465594	BY481P LED250S/840 PSD WB GC WH BR	-	-	-	Wide beam

GentleSpace Gen3

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
910500465801	BY480P LED130S/840 PSD NBA GC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam
910500465802	BY480P LED170S/840 PSD NBA GC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam
910500465803	BY481P LED250S/840 PSD NBA GC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam
910500465804	BY481P LED350S/840 PSD NBA GC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
910500465805	BY481P LED350S/840 PSD NBA PC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam
910500465806	BY481P LED250S/840 PSD NBA PC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam
910500465807	BY480P LED130S/840 PSD NBA PC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam
910500465808	BY480P LED170S/840 PSD NBA PC SI	-	Polymethyl methacrylate bowl/cover	-	Wide beam

General Information (2/2)

Order Code	Full Product Name	Product Family Code	UL mark
910500465536	BY481P LED250S/840 PSD WB GC SI	BY481P	-
910500465537	BY481P LED250S/840 PSD MB GC SI	BY481P	-
910500465538	BY481P LED350S/840 PSD MB GC SI	BY481P	-
910500465540	BY481P LED250S/840 PSD NB GC SI	BY481P	-
910500465547	BY481P LED250S/840 PSD WB PC SI	BY481P	-
910500465549	BY481P LED350S/840 PSD WB GC SI	BY481P	-
910500465550	BY481P LED250S/840 PSD MB PC SI	BY481P	-
910500465569	BY481P LED250S/840 PSD HRO GC SI	BY481P	-
910500465573	BY481P LED350S/840 PSD HRO GC SI	BY481P	-
910500465574	BY481P LED350S/840 PSD NB GC SI	BY481P	-
910500465575	BY481P LED250S/840 PSD HRO PC SI	BY481P	-
910500465599	BY481P LED350S/840 PSD WB PC SI	BY481P	-
910500465602	BY481P LED250S/840 PSD NB PC SI	BY481P	-
910500465605	BY481P LED350S/840 PSD MB PC SI	BY481P	-
910500465606	BY481P LED350S/840 PSD HRO PC SI	BY481P	-
910500465539	BY480P LED130S/840 PSD WB GC SI	BY481P	-
910500465542	BY480P LED170S/840 PSD WB GC SI	BY480P	-
910500465544	BY480P LED130S/840 PSD MB GC SI	BY480P	-
910500465545	BY480P LED170S/840 PSD HRO GC SI	BY480P	-
910500465548	BY480P LED130S/840 PSD HRO GC SI	BY480P	-
910500465551	BY480P LED170S/840 PSD MB GC SI	BY480P	-
910500465568	BY480P LED130S/840 PSD WB PC SI	BY480P	-
910500465579	BY480P LED170S/840 PSD NB GC SI	BY480P	-
910500465580	BY480P LED170S/840 PSD WB PC SI	BY480P	-
910500465589	BY480P LED130S/840 PSD NB PC SI	BY480P	-
910500465591	BY480P LED130S/840 PSD NB GC SI	BY480P	-
910500465593	BY480P LED130S/840 PSD HRO PC SI	BY480P	-
910500465595	BY480P LED170S/840 PSD MB PC SI	BY480P	-
910500465597	BY480P LED130S/840 PSD MB PC SI	BY480P	-
910500465603	BY480P LED170S/840 PSD HRO PC SI	BY480P	-
910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	BY481X	-
910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	BY481X	-
910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	BY481X	-

Order Code	Full Product Name	Product Family Code	UL mark
910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	BY481X	-
910500465556	BY481P LED250S/840 PSD MB GC SI BR	BY481P	-
910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	BY481X	-
910500465564	BY481P LED250S/840 PSD WB GC SI BR	BY481P	-
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	BY481X	-
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	BY481X	-
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	BY481X	-
910500465584	BY481P LED250S/840 PSD NB GC SI BR	BY481P	-
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	BY481P	-
910500465596	BY481P LED350S/840 PSD MB GC SI BR	BY481P	-
910500465608	BY481P LED350S/840 PSD WB GC SI BR	BY481P	-
910500465546	BY480P LED170S/840 PSD MB GC WH BR	BY480P	-
910500465570	BY480P LED170S/840 PSD WB GC WH BR	BY480P	-
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	BY480X	-
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	BY480X	-
910500465558	BY480P LED170S/840 PSD WB GC SI BR	BY480P	-
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	BY480X	-
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	BY480X	-
910500465561	BY480P LED130S/840 PSD MB GC SI BR	BY480P	-
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	BY480X	-
910500465572	BY480P LED130S/840 PSD WB GC SI BR	BY480P	-
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	BY480X	-
910500465585	BY480P LED170S/840 PSD MB GC SI BR	BY480P	-
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	BY480P	-
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	BY480X	-
910500465604	BY480P LED170S/840 PSD NB GC SI BR	BY480P	-
910500465563	BY481P LED250S/840 PSD MB GC WH	BY481P	-
910500465577	BY481P LED250S/840 PSD MB PC WH	BY481P	-
910500465583	BY481P LED250S/840 PSD WB GC WH	BY481P	-
910500465607	BY481P LED250S/840 PSD HRO GC WH	BY481P	-
910500465566	BY480P LED130S/840 PSD WB GC WH	BY480P	-
910500465578	BY480P LED170S/840 PSD MB GC WH	BY480P	-
910500465581	BY480P LED170S/840 PSD WB GC WH	BY480P	-

Order Code	Full Product Name	Product	
		Family Code	UL mark
910500465582	BY480P LED130S/840 PSD MB GC WH	BY480P	-
910500465586	BY480P LED170S/840 PSD HRO GC WH	BY480P	-
910500465588	BY480P LED170S/840 PSD NB GC WH	BY480P	-
910500465609	BY480P LED170S/840 PSD WB PC WH	BY480P	-
910500465587	BY481P LED250S/840 PSD MB GC WH BR	BY481P	-
910500465594	BY481P LED250S/840 PSD WB GC WH BR	BY481P	-
910500465801	BY480P LED130S/840 PSD NBA GC SI	BY480P	-

Order Code	Full Product Name	Product	
		Family Code	UL mark
910500465802	BY480P LED170S/840 PSD NBA GC SI	BY480P	-
910500465803	BY481P LED250S/840 PSD NBA GC SI	BY480P	-
910500465804	BY481P LED350S/840 PSD NBA GC SI	BY480P	-
910500465805	BY481P LED350S/840 PSD NBA PC SI	BY480P	-
910500465806	BY481P LED250S/840 PSD NBA PC SI	BY480P	-
910500465807	BY480P LED130S/840 PSD NBA PC SI	BY480P	-
910500465808	BY480P LED170S/840 PSD NBA PC SI	BY480P	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910500465536	BY481P LED250S/840 PSD WB GC SI	154 lm/W	25000 lm	162 W
910500465537	BY481P LED250S/840 PSD MB GC SI	154 lm/W	25000 lm	162 W
910500465538	BY481P LED350S/840 PSD MB GC SI	148 lm/W	35000 lm	236 W
910500465540	BY481P LED250S/840 PSD NB GC SI	154 lm/W	25000 lm	162 W
910500465547	BY481P LED250S/840 PSD WB PC SI	154 lm/W	25000 lm	162 W
910500465549	BY481P LED350S/840 PSD WB GC SI	148 lm/W	35000 lm	236 W
910500465550	BY481P LED250S/840 PSD MB PC SI	154 lm/W	25000 lm	162 W
910500465569	BY481P LED250S/840 PSD HRO GC SI	154 lm/W	25000 lm	162 W
910500465573	BY481P LED350S/840 PSD HRO GC SI	148 lm/W	35000 lm	236 W
910500465574	BY481P LED350S/840 PSD NB GC SI	148 lm/W	35000 lm	236 W
910500465575	BY481P LED250S/840 PSD HRO PC SI	154 lm/W	25000 lm	162 W
910500465599	BY481P LED350S/840 PSD WB PC SI	148 lm/W	35000 lm	236 W
910500465602	BY481P LED250S/840 PSD NB PC SI	154 lm/W	25000 lm	162 W
910500465605	BY481P LED350S/840 PSD MB PC SI	148 lm/W	35000 lm	236 W
910500465606	BY481P LED350S/840 PSD HRO PC SI	148 lm/W	35000 lm	236 W
910500465539	BY480P LED130S/840 PSD WB GC SI	153 lm/W	13000 lm	85 W
910500465542	BY480P LED170S/840 PSD WB GC SI	142 lm/W	17000 lm	120 W
910500465544	BY480P LED130S/840 PSD MB GC SI	153 lm/W	13000 lm	85 W
910500465545	BY480P LED170S/840 PSD HRO GC SI	142 lm/W	17000 lm	120 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910500465548	BY480P LED130S/840 PSD HRO GC SI	153 lm/W	13000 lm	85 W
910500465551	BY480P LED170S/840 PSD MB GC SI	142 lm/W	17000 lm	120 W
910500465568	BY480P LED130S/840 PSD WB PC SI	153 lm/W	13000 lm	85 W
910500465579	BY480P LED170S/840 PSD NB GC SI	142 lm/W	17000 lm	120 W
910500465580	BY480P LED170S/840 PSD WB PC SI	142 lm/W	17000 lm	120 W
910500465589	BY480P LED130S/840 PSD NB PC SI	153 lm/W	13000 lm	85 W
910500465591	BY480P LED130S/840 PSD NB GC SI	153 lm/W	13000 lm	85 W
910500465593	BY480P LED130S/840 PSD HRO PC SI	153 lm/W	13000 lm	85 W
910500465595	BY480P LED170S/840 PSD MB PC SI	142 lm/W	17000 lm	120 W
910500465597	BY480P LED130S/840 PSD MB PC SI	153 lm/W	13000 lm	85 W
910500465603	BY480P LED170S/840 PSD HRO PC SI	142 lm/W	17000 lm	120 W
910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	154 lm/W	25000 lm	162 W
910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	154 lm/W	25000 lm	162 W
910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	154 lm/W	25000 lm	162 W
910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	148 lm/W	35000 lm	236 W
910500465556	BY481P LED250S/840 PSD MB GC SI BR	154 lm/W	25000 lm	162 W
910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	148 lm/W	35000 lm	236 W
910500465564	BY481P LED250S/840 PSD WB GC SI BR	154 lm/W	25000 lm	162 W
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	148 lm/W	35000 lm	236 W

GentleSpace Gen3

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	154 lm/W	25000 lm	162 W
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	148 lm/W	35000 lm	236 W
910500465584	BY481P LED250S/840 PSD NB GC SI BR	154 lm/W	25000 lm	162 W
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	154 lm/W	25000 lm	162 W
910500465596	BY481P LED350S/840 PSD MB GC SI BR	148 lm/W	35000 lm	236 W
910500465608	BY481P LED350S/840 PSD WB GC SI BR	148 lm/W	35000 lm	236 W
910500465546	BY480P LED170S/840 PSD MB GC WH BR	142 lm/W	17000 lm	120 W
910500465570	BY480P LED170S/840 PSD WB GC WH BR	142 lm/W	17000 lm	120 W
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	153 lm/W	13000 lm	85 W
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	142 lm/W	17000 lm	120 W
910500465558	BY480P LED170S/840 PSD WB GC SI BR	142 lm/W	17000 lm	120 W
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	142 lm/W	17000 lm	120 W
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	153 lm/W	13000 lm	85 W
910500465561	BY480P LED130S/840 PSD MB GC SI BR	153 lm/W	13000 lm	85 W
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	153 lm/W	13000 lm	85 W
910500465572	BY480P LED130S/840 PSD WB GC SI BR	153 lm/W	13000 lm	85 W
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	142 lm/W	17000 lm	120 W
910500465585	BY480P LED170S/840 PSD MB GC SI BR	142 lm/W	17000 lm	120 W
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	153 lm/W	13000 lm	85 W
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	153 lm/W	13000 lm	85 W
910500465604	BY480P LED170S/840 PSD NB GC SI BR	142 lm/W	17000 lm	120 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910500465563	BY481P LED250S/840 PSD MB GC WH	154 lm/W	25000 lm	162 W
910500465577	BY481P LED250S/840 PSD MB PC WH	154 lm/W	25000 lm	162 W
910500465583	BY481P LED250S/840 PSD WB GC WH	154 lm/W	25000 lm	162 W
910500465607	BY481P LED250S/840 PSD HRO GC WH	154 lm/W	25000 lm	162 W
910500465566	BY480P LED130S/840 PSD WB GC WH	153 lm/W	13000 lm	85 W
910500465578	BY480P LED170S/840 PSD MB GC WH	142 lm/W	17000 lm	120 W
910500465581	BY480P LED170S/840 PSD WB GC WH	142 lm/W	17000 lm	120 W
910500465582	BY480P LED130S/840 PSD MB GC WH	153 lm/W	13000 lm	85 W
910500465586	BY480P LED170S/840 PSD HRO GC WH	142 lm/W	17000 lm	120 W
910500465588	BY480P LED170S/840 PSD NB GC WH	142 lm/W	17000 lm	120 W
910500465609	BY480P LED170S/840 PSD WB PC WH	142 lm/W	17000 lm	120 W
910500465587	BY481P LED250S/840 PSD MB GC WH BR	154 lm/W	25000 lm	162 W
910500465594	BY481P LED250S/840 PSD WB GC WH BR	154 lm/W	25000 lm	162 W
910500465801	BY480P LED130S/840 PSD NBA GC SI	155 lm/W	13000 lm	84 W
910500465802	BY480P LED170S/840 PSD NBA GC SI	142 lm/W	17000 lm	120 W
910500465803	BY481P LED250S/840 PSD NBA GC SI	154 lm/W	25000 lm	162 W
910500465804	BY481P LED350S/840 PSD NBA GC SI	151 lm/W	35000 lm	232 W
910500465805	BY481P LED350S/840 PSD NBA PC SI	151 lm/W	35000 lm	232 W
910500465806	BY481P LED250S/840 PSD NBA PC SI	154 lm/W	25000 lm	162 W
910500465807	BY480P LED130S/840 PSD NBA PC SI	155 lm/W	13000 lm	84 W
910500465808	BY480P LED170S/840 PSD NBA PC SI	142 lm/W	17000 lm	120 W

Mechanical and Housing

Order Code	Full Product Name	Color	Diameter
910500465536	BY481P LED250S/840 PSD WB GC SI	Silver	-
910500465537	BY481P LED250S/840 PSD MB GC SI	Silver	-
910500465538	BY481P LED350S/840 PSD MB GC SI	Silver	-
910500465540	BY481P LED250S/840 PSD NB GC SI	Silver	-

Order Code	Full Product Name	Color	Diameter
910500465547	BY481P LED250S/840 PSD WB PC SI	Silver	-
910500465549	BY481P LED350S/840 PSD WB GC SI	Silver	-
910500465550	BY481P LED250S/840 PSD MB PC SI	Silver	-
910500465569	BY481P LED250S/840 PSD HRO GC SI	Silver	-

GentleSpace Gen3

Order Code	Full Product Name	Color	Diameter
910500465573	BY481P LED350S/840 PSD HRO GC SI	Silver	-
910500465574	BY481P LED350S/840 PSD NB GC SI	Silver	-
910500465575	BY481P LED250S/840 PSD HRO PC SI	Silver	-
910500465599	BY481P LED350S/840 PSD WB PC SI	Silver	-
910500465602	BY481P LED250S/840 PSD NB PC SI	Silver	-
910500465605	BY481P LED350S/840 PSD MB PC SI	Silver	-
910500465606	BY481P LED350S/840 PSD HRO PC SI	Silver	-
910500465539	BY480P LED130S/840 PSD WB GC SI	Silver	-
910500465542	BY480P LED170S/840 PSD WB GC SI	Silver	-
910500465544	BY480P LED130S/840 PSD MB GC SI	Silver	-
910500465545	BY480P LED170S/840 PSD HRO GC SI	Silver	-
910500465548	BY480P LED130S/840 PSD HRO GC SI	Silver	-
910500465551	BY480P LED170S/840 PSD MB GC SI	Silver	-
910500465568	BY480P LED130S/840 PSD WB PC SI	Silver	-
910500465579	BY480P LED170S/840 PSD NB GC SI	Silver	-
910500465580	BY480P LED170S/840 PSD WB PC SI	Silver	-
910500465589	BY480P LED130S/840 PSD NB PC SI	Silver	-
910500465591	BY480P LED130S/840 PSD NB GC SI	Silver	-
910500465593	BY480P LED130S/840 PSD HRO PC SI	Silver	-
910500465595	BY480P LED170S/840 PSD MB PC SI	Silver	-
910500465597	BY480P LED130S/840 PSD MB PC SI	Silver	-
910500465603	BY480P LED170S/840 PSD HRO PC SI	Silver	-
910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	Silver	-
910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	Silver	-
910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	Silver	-
910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	Silver	-
910500465556	BY481P LED250S/840 PSD MB GC SI BR	Silver	-
910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	Silver	-
910500465564	BY481P LED250S/840 PSD WB GC SI BR	Silver	-
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	Silver	-
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	Silver	-
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	Silver	-
910500465584	BY481P LED250S/840 PSD NB GC SI BR	Silver	-
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	Silver	-
910500465596	BY481P LED350S/840 PSD MB GC SI BR	Silver	-
910500465608	BY481P LED350S/840 PSD WB GC SI BR	Silver	-

Order Code	Full Product Name	Color	Diameter
910500465546	BY480P LED170S/840 PSD MB GC WH BR	White	-
910500465570	BY480P LED170S/840 PSD WB GC WH BR	White	-
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	Silver	-
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	Silver	-
910500465558	BY480P LED170S/840 PSD WB GC SI BR	Silver	-
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	Silver	-
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	Silver	-
910500465561	BY480P LED130S/840 PSD MB GC SI BR	Silver	-
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	Silver	-
910500465572	BY480P LED130S/840 PSD WB GC SI BR	Silver	-
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	Silver	-
910500465585	BY480P LED170S/840 PSD MB GC SI BR	Silver	-
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	Silver	-
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	Silver	-
910500465604	BY480P LED170S/840 PSD NB GC SI BR	Silver	-
910500465563	BY481P LED250S/840 PSD MB GC WH	White	-
910500465577	BY481P LED250S/840 PSD MB PC WH	White	-
910500465583	BY481P LED250S/840 PSD WB GC WH	White	-
910500465607	BY481P LED250S/840 PSD HRO GC WH	White	-
910500465566	BY480P LED130S/840 PSD WB GC WH	White	-
910500465578	BY480P LED170S/840 PSD MB GC WH	White	-
910500465581	BY480P LED170S/840 PSD WB GC WH	White	-
910500465582	BY480P LED130S/840 PSD MB GC WH	White	-
910500465586	BY480P LED170S/840 PSD HRO GC WH	White	-
910500465588	BY480P LED170S/840 PSD NB GC WH	White	-
910500465609	BY480P LED170S/840 PSD WB PC WH	White	-
910500465587	BY481P LED250S/840 PSD MB GC WH BR	White	-
910500465594	BY481P LED250S/840 PSD WB GC WH BR	White	-
910500465801	BY480P LED130S/840 PSD NBA GC SI	Silver	-
910500465802	BY480P LED170S/840 PSD NBA GC SI	Silver	-
910500465803	BY481P LED250S/840 PSD NBA GC SI	Silver	-
910500465804	BY481P LED350S/840 PSD NBA GC SI	Silver	-
910500465805	BY481P LED350S/840 PSD NBA PC SI	Silver	-
910500465806	BY481P LED250S/840 PSD NBA PC SI	Silver	-
910500465807	BY480P LED130S/840 PSD NBA PC SI	Silver	-
910500465808	BY480P LED170S/840 PSD NBA PC SI	Silver	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50
910500465536	BY481P LED250S/840 PSD WB GC SI	70000 h
910500465537	BY481P LED250S/840 PSD MB GC SI	100000 h
910500465538	BY481P LED350S/840 PSD MB GC SI	100000 h
910500465540	BY481P LED250S/840 PSD NB GC SI	100000 h
910500465547	BY481P LED250S/840 PSD WB PC SI	100000 h
910500465549	BY481P LED350S/840 PSD WB GC SI	100000 h
910500465550	BY481P LED250S/840 PSD MB PC SI	100000 h
910500465569	BY481P LED250S/840 PSD HRO GC SI	100000 h
910500465573	BY481P LED350S/840 PSD HRO GC SI	100000 h
910500465574	BY481P LED350S/840 PSD NB GC SI	100000 h
910500465575	BY481P LED250S/840 PSD HRO PC SI	100000 h

Order Code	Full Product Name	Median useful life L80B50
910500465599	BY481P LED350S/840 PSD WB PC SI	100000 h
910500465602	BY481P LED250S/840 PSD NB PC SI	100000 h
910500465605	BY481P LED350S/840 PSD MB PC SI	100000 h
910500465606	BY481P LED350S/840 PSD HRO PC SI	100000 h
910500465539	BY480P LED130S/840 PSD WB GC SI	100000 h
910500465542	BY480P LED170S/840 PSD WB GC SI	100000 h
910500465544	BY480P LED130S/840 PSD MB GC SI	100000 h
910500465545	BY480P LED170S/840 PSD HRO GC SI	100000 h
910500465548	BY480P LED130S/840 PSD HRO GC SI	100000 h
910500465551	BY480P LED170S/840 PSD MB GC SI	100000 h
910500465568	BY480P LED130S/840 PSD WB PC SI	100000 h

GentleSpace Gen3

Order Code	Full Product Name	Median useful life L80B50
910500465579	BY480P LED170S/840 PSD NB GC SI	100000 h
910500465580	BY480P LED170S/840 PSD WB PC SI	100000 h
910500465589	BY480P LED130S/840 PSD NB PC SI	100000 h
910500465591	BY480P LED130S/840 PSD NB GC SI	100000 h
910500465593	BY480P LED130S/840 PSD HRO PC SI	100000 h
910500465595	BY480P LED170S/840 PSD MB PC SI	100000 h
910500465597	BY480P LED130S/840 PSD MB PC SI	100000 h
910500465603	BY480P LED170S/840 PSD HRO PC SI	100000 h
910500465541	BY481X LED250S/840 MB GC SI ACW-L BR	100000 h
910500465543	BY481X LED250S/840 WB GC SI ACW-L BR	100000 h
910500465553	BY481X LED250S/840 HRO GC SI ACW-L BR	100000 h
910500465555	BY481X LED350S/840 MB GC SI ACW-L BR	100000 h
910500465556	BY481P LED250S/840 PSD MB GC SI BR	100000 h
910500465557	BY481X LED350S/840 WB GC SI ACW-L BR	100000 h
910500465564	BY481P LED250S/840 PSD WB GC SI BR	100000 h
910500465565	BY481X LED350S/840 HRO GC SI ACW-L BR	100000 h
910500465567	BY481X LED250S/840 NB GC SI ACW-L BR	100000 h
910500465571	BY481X LED350S/840 NB GC SI ACW-L BR	100000 h
910500465584	BY481P LED250S/840 PSD NB GC SI BR	100000 h
910500465592	BY481P LED250S/840 PSD HRO GC SI BR	100000 h
910500465596	BY481P LED350S/840 PSD MB GC SI BR	100000 h
910500465608	BY481P LED350S/840 PSD WB GC SI BR	100000 h
910500465546	BY480P LED170S/840 PSD MB GC WH BR	100000 h
910500465570	BY480P LED170S/840 PSD WB GC WH BR	100000 h
910500465552	BY480X LED130S/840 HRO GC SI ACW-L BR	100000 h
910500465554	BY480X LED170S/840 WB GC SI ACW-L BR	100000 h
910500465558	BY480P LED170S/840 PSD WB GC SI BR	100000 h
910500465559	BY480X LED170S/840 MB GC SI ACW-L BR	100000 h
910500465560	BY480X LED130S/840 WB GC SI ACW-L BR	100000 h

Order Code	Full Product Name	Median useful life L80B50
910500465561	BY480P LED130S/840 PSD MB GC SI BR	100000 h
910500465562	BY480X LED130S/840 MB GC SI ACW-L BR	100000 h
910500465572	BY480P LED130S/840 PSD WB GC SI BR	100000 h
910500465576	BY480X LED170S/840 HRO GC SI ACW-L BR	100000 h
910500465585	BY480P LED170S/840 PSD MB GC SI BR	100000 h
910500465590	BY480P LED130S/840 PSD HRO GC SI BR	100000 h
910500465601	BY480X LED130S/840 NB GC SI ACW-L BR	100000 h
910500465604	BY480P LED170S/840 PSD NB GC SI BR	100000 h
910500465563	BY481P LED250S/840 PSD MB GC WH	100000 h
910500465577	BY481P LED250S/840 PSD MB PC WH	100000 h
910500465583	BY481P LED250S/840 PSD WB GC WH	100000 h
910500465607	BY481P LED250S/840 PSD HRO GC WH	100000 h
910500465566	BY480P LED130S/840 PSD WB GC WH	100000 h
910500465578	BY480P LED170S/840 PSD MB GC WH	100000 h
910500465581	BY480P LED170S/840 PSD WB GC WH	100000 h
910500465582	BY480P LED130S/840 PSD MB GC WH	100000 h
910500465586	BY480P LED170S/840 PSD HRO GC WH	100000 h
910500465588	BY480P LED170S/840 PSD NB GC WH	100000 h
910500465609	BY480P LED170S/840 PSD WB PC WH	100000 h
910500465587	BY481P LED250S/840 PSD MB GC WH BR	100000 h
910500465594	BY481P LED250S/840 PSD WB GC WH BR	100000 h
910500465801	BY480P LED130S/840 PSD NBA GC SI	70000 h
910500465802	BY480P LED170S/840 PSD NBA GC SI	70000 h
910500465803	BY481P LED250S/840 PSD NBA GC SI	70000 h
910500465804	BY481P LED350S/840 PSD NBA GC SI	70000 h
910500465805	BY481P LED350S/840 PSD NBA PC SI	70000 h
910500465806	BY481P LED250S/840 PSD NBA PC SI	70000 h
910500465807	BY480P LED130S/840 PSD NBA PC SI	70000 h
910500465808	BY480P LED170S/840 PSD NBA PC SI	70000 h

