



# 高性能射灯可用于改造 MR16 卤素灯

## MASTER LEDspot LV

MASTER LEDspot LV 提供强烈的重点光束，对于聚光照明而言，它是一个理想的翻新改造解决方案。MASTER LEDspot LV 设计用于替代卤素灯或白炽聚光灯。它能呈现出自然的颜色，为住宅和酒店营造出温暖舒适的氛围，凸显出零售商品的美感。更小巧的新外壳可通过一个 MR16 GU 5.3 支座与市面上出售的大部分灯具完美适配。它不仅采用了飞利浦专利解决方案来保证与各种标准 12V 电子卤素变压器广泛兼容，还能提供与 MR16 卤素聚光灯相当的光束强度。它具备调光功能，能够营造出您想要的氛围，并且兼容广泛的调光器。它极高的 SDCM 确保在整个产品使用寿命期间能够保持更好的颜色一致性。MASTER LEDspot LV 节约了大量能源，最大限度地降低了维护成本，而灯光质量和使用寿命丝毫不减，使住宅和商铺业主能够在短时间内获得投资回报。

### 优点

- 高强度光束可用于专业应用中的重点照明
- 在很长时间内保持极高亮度
- 更加自然的色彩为宾馆营造出舒适温暖的格调，在商场照明应用中可达到更好的推广展示效果

### 特点

- 高强度光束可与卤素灯相媲美
- 高显色指数呈现出更好的色彩效果，在很长时间内保持高度的颜色一致性
- 定位清晰的光束扩散实现重点照明
- 兼容各类变压器，对于可调光产品实现均匀调光
- 高光通维持率，使用寿命长达 40,000 小时

### 应用

- 家庭照明：客厅、卧室、门厅
- 酒店照明：酒店客房、走廊、大厅、接待区、餐厅、酒吧、咖啡厅
- 商场照明：展厅、展示柜、店铺、更衣室、结账区

# MASTER LEDspot LV


## Versions



7-50W GU5-3 MR16

50W GU5-3 MR16

## 二维绘图



| Product                                 | D       | C       |
|-----------------------------------------|---------|---------|
| MASTER LED 6.5-50W 927 MR16 10D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 927 MR16 24D CN      | 50.5 mm | 46.5 mm |
| MASTER LED 6.5-50W 927 MR16 24D Dim CN  | 50 mm   |         |
| MASTER LED 6.5-50W 927 MR16 36D CN      | 50.5 mm | 46.5 mm |
| MASTER LED 6.5-50W 927 MR16 36D Dim CN  | 50 mm   |         |
| MASTER LED 6.5-50W 927 MR16 60D Dim     | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 930 MR16 10D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 930 MR16 24D CN      | 50.5 mm | 46.5 mm |
| MASTER LED 6.5-50W 930 MR16 24D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 930 MR16 36D CN      | 50.5 mm | 46.5 mm |
| MASTER LED 6.5-50W 930 MR16 36D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 930 MR16 60D Dim     | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 940 MR16 10D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 940 MR16 24D CN      | 50.5 mm | 46.5 mm |
| MASTER LED 6.5-50W 940 MR16 24D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 940 MR16 36D Dim CN  | 50 mm   | 46.5 mm |
| MASTER LED 6.5-50W 940 MR16 60D Dim     | 50 mm   | 46.5 mm |
| MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | 50 mm   | 46.5 mm |
| MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | 50 mm   | 46.5 mm |
| MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | 50 mm   | 46.5 mm |
| MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | 50 mm   | 46.5 mm |

| 一般信息                    |           |
|-------------------------|-----------|
| 底盖                      | GU5.3     |
| 切换循环                    | 50,000    |
| 标称使用寿命                  | 40,000 小时 |
| 灯技术                     |           |
| 标称使用寿命结束时灯的光通维持率 ( 标称 ) | 70 %      |
| 操作和电气                   |           |
| 输入频率                    | - Hz      |
| 线频率                     | - Hz      |
| 启动时间 ( 标称 )             | 0.5 s     |
| 瓦数相当                    | 50 W      |
| 机械和外壳                   |           |
| 灯泡外形                    | MR16      |

灯技术 (1/2)

| Order Code   | Full Product Name                       | 光束角度 ( 标称 )       |        | 显色指数 |     |
|--------------|-----------------------------------------|-------------------|--------|------|-----|
|              |                                         | 相关色温 ( 标称 ) (CRI) |        | 颜色代码 |     |
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN      | 24 °              | 2700 K | 90   | 927 |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN      | 24 °              | 3000 K | 90   | 930 |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN      | 24 °              | 4000 K | 90   | 940 |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN  | 24 °              | 2700 K | 90   | 927 |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN  | 24 °              | 3000 K | 90   | 930 |
| 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN  | 24 °              | 4000 K | 90   | 940 |
| 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN  | 36 °              | 2700 K | 90   | 927 |
| 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN  | 36 °              | 3000 K | 90   | 930 |
| 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN  | 36 °              | 4000 K | 90   | 940 |
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | 24 °              | 2700 K | 80   | 827 |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | 24 °              | 3000 K | 80   | 830 |
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | 36 °              | 2700 K | 80   | 827 |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | 36 °              | 3000 K | 80   | 830 |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | 10 °              | 2700 K | 90   | 927 |
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN  | 10 °              | 3000 K | 90   | 930 |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN  | 10 °              | 4000 K | 90   | 940 |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN      | 36 °              | 2700 K | 90   | 927 |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN      | 36 °              | 3000 K | 90   | 930 |
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim     | 60 °              | 2700 K | 90   | 927 |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim     | 60 °              | 3000 K | 90   | 930 |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim     | 60 °              | 4000 K | 90   | 940 |

灯技术 (2/2)

| Order Code   | Full Product Name                      | 光通量    | 发光强度 ( 标称 ) | Order Code   | Full Product Name                      | 光通量    | 发光强度 ( 标称 ) |
|--------------|----------------------------------------|--------|-------------|--------------|----------------------------------------|--------|-------------|
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN     | 470 lm | 2,300 cd    | 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN | 530 lm | 3,400 cd    |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN     | 470 lm | 2,300 cd    | 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN | 500 lm | 1,400 cd    |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN     | 520 lm | 2,500 cd    | 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN | 500 lm | 1,600 cd    |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN | 500 lm | 2,800 cd    | 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN | 530 lm | 1,600 cd    |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN | 500 lm | 2,800 cd    |              |                                        |        |             |

MASTER LEDspot LV

| Order Code   | Full Product Name                       | 光通量    | 发光强度 ( 标称 ) |
|--------------|-----------------------------------------|--------|-------------|
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | 660 lm | 3,100 cd    |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | 660 lm | 3,250 cd    |
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | 660 lm | 1,700 cd    |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | 660 lm | 1,700 cd    |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | 500 lm | 5,300 cd    |

| Order Code   | Full Product Name                      | 光通量    | 发光强度 ( 标称 ) |
|--------------|----------------------------------------|--------|-------------|
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN | 500 lm | 5,300 cd    |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN | 530 lm | 5,600 cd    |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN     | 470 lm | 1,400 cd    |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN     | 470 lm | 1,400 cd    |
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim    | 500 lm | 500 cd      |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim    | 500 lm | 500 cd      |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim    | 530 lm | 550 cd      |

操作和电气

| Order Code   | Full Product Name                       | 功耗    |
|--------------|-----------------------------------------|-------|
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN      | 6.5 W |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN      | 6.5 W |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN      | 6.5 W |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN  | 6.5 W |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN  | 6.5 W |
| 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN  | 6.5 W |
| 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN  | 6.5 W |
| 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN  | 6.5 W |
| 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN  | 6.5 W |
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | 7.5 W |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | 7.5 W |

| Order Code   | Full Product Name                       | 功耗    |
|--------------|-----------------------------------------|-------|
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | 7.5 W |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | 7.5 W |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | 6.5 W |
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN  | 6.5 W |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN  | 6.5 W |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN      | 6.5 W |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN      | 6.5 W |
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim     | 6.5 W |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim     | 6.5 W |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim     | 6.5 W |

温度

| Order Code   | Full Product Name                       | 最大外壳温度 ( 标称 ) |
|--------------|-----------------------------------------|---------------|
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN      | 90 °C         |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN      | 90 °C         |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN      | 90 °C         |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN  | 90 °C         |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN  | 90 °C         |
| 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN  | 90 °C         |
| 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN  | 90 °C         |
| 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN  | 90 °C         |
| 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN  | 90 °C         |
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | 93 °C         |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | 93 °C         |

| Order Code   | Full Product Name                       | 最大外壳温度 ( 标称 ) |
|--------------|-----------------------------------------|---------------|
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | 93 °C         |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | 93 °C         |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | 90 °C         |
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN  | 90 °C         |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN  | 90 °C         |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN      | 90 °C         |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN      | 90 °C         |
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim     | 90 °C         |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim     | 90 °C         |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim     | 90 °C         |

控制和调光

| Order Code   | Full Product Name                      | 可调光        |
|--------------|----------------------------------------|------------|
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN     | 否          |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN     | 否          |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN     | 否          |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN | 仅限于使用特定调光器 |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN | 仅限于使用特定调光器 |
| 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN | 仅限于使用特定调光器 |
| 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN | 仅限于使用特定调光器 |

| Order Code   | Full Product Name                       | 可调光        |
|--------------|-----------------------------------------|------------|
| 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN  | 仅限于使用特定调光器 |
| 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN  | 仅限于使用特定调光器 |
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | 仅限于使用特定调光器 |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | 仅限于使用特定调光器 |
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | 仅限于使用特定调光器 |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | 仅限于使用特定调光器 |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | 仅限于使用特定调光器 |

MASTER LEDspot LV

| Order Code   | Full Product Name                      | 可调光        |
|--------------|----------------------------------------|------------|
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN | 仅限于使用特定调光器 |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN | 仅限于使用特定调光器 |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN     | 否          |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN     | 否          |

机械和外壳


| Order Code   | Full Product Name                       | 灯泡外观 |
|--------------|-----------------------------------------|------|
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN      | 透明   |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN      | 透明   |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN      | 透明   |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN  | -    |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN  | -    |
| 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN  | -    |
| 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN  | -    |
| 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN  | -    |
| 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN  | -    |
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | -    |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | -    |


审批和申请







| Order Code   | Full Product Name                       | 能耗 kWh/1000 h |
|--------------|-----------------------------------------|---------------|
| 929001881910 | MASTER LED 6.5-50W 927 MR16 24D CN      | 8 kWh         |
| 929001882010 | MASTER LED 6.5-50W 930 MR16 24D CN      | 8 kWh         |
| 929001882110 | MASTER LED 6.5-50W 940 MR16 24D CN      | 8 kWh         |
| 929003071910 | MASTER LED 6.5-50W 927 MR16 24D Dim CN  | -             |
| 929003072010 | MASTER LED 6.5-50W 930 MR16 24D Dim CN  | -             |
| 929003072110 | MASTER LED 6.5-50W 940 MR16 24D Dim CN  | -             |
| 929003072210 | MASTER LED 6.5-50W 927 MR16 36D Dim CN  | -             |
| 929003072310 | MASTER LED 6.5-50W 930 MR16 36D Dim CN  | -             |
| 929003072410 | MASTER LED 6.5-50W 940 MR16 36D Dim CN  | -             |
| 929003072510 | MASTER LED 7.5-50W+ 827 MR16 24D Dim CN | -             |
| 929003072610 | MASTER LED 7.5-50W+ 830 MR16 24D Dim CN | -             |
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | -             |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | -             |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | -             |
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN  | -             |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN  | -             |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN      | 8 kWh         |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN      | 8 kWh         |
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim     | -             |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim     | -             |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim     | -             |

| Order Code   | Full Product Name                   | 可调光        |
|--------------|-------------------------------------|------------|
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim | 仅限于使用特定调光器 |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim | 仅限于使用特定调光器 |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim | 仅限于使用特定调光器 |

| Order Code   | Full Product Name                       | 灯泡外观 |
|--------------|-----------------------------------------|------|
| 929003072710 | MASTER LED 7.5-50W+ 827 MR16 36D Dim CN | -    |
| 929003072810 | MASTER LED 7.5-50W+ 830 MR16 36D Dim CN | -    |
| 929003071610 | MASTER LED 6.5-50W 927 MR16 10D Dim CN  | -    |
| 929003071710 | MASTER LED 6.5-50W 930 MR16 10D Dim CN  | -    |
| 929003071810 | MASTER LED 6.5-50W 940 MR16 10D Dim CN  | -    |
| 929001882210 | MASTER LED 6.5-50W 927 MR16 36D CN      | 透明   |
| 929001882310 | MASTER LED 6.5-50W 930 MR16 36D CN      | 透明   |
| 929003075908 | MASTER LED 6.5-50W 927 MR16 60D Dim     | -    |
| 929003076008 | MASTER LED 6.5-50W 930 MR16 60D Dim     | -    |
| 929003076108 | MASTER LED 6.5-50W 940 MR16 60D Dim     | -    |














Accent Diagrams




Accent Diagram - MASTER LED 6.5-50W 930  
MR16 24D Dim CN




Accent Diagram - MASTER LED 6.5-50W 940  
MR16 24D CN




Accent Diagram - MASTER LED 6.5-50W 930  
MR16 36D Dim CN




Accent Diagram - MASTER LED 6.5-50W 930  
MR16 10D Dim CN




Accent Diagram - MASTER LED 6.5-50W 927  
MR16 24D Dim CN




Accent Diagram - MASTER LED 6.5-50W 940  
MR16 10D Dim CN



Accent Diagram - MASTER LED 7.5-50W+ 830  
MR16 24D Dim CN




Accent Diagram - MASTER LED 6.5-50W 927  
MR16 10D Dim CN




Accent Diagram - MASTER LED 6.5-50W 940  
MR16 36D Dim CN

Accent Diagrams




Accent Diagram - MASTER LED 6.5-50W 940  
MR16 24D Dim CN




Accent Diagram - MASTER LED 7.5-50W+ 830  
MR16 36D Dim CN


Accent Diagram - MASTER LED 6.5-50W 927  
MR16 36D Dim CN




Accent Diagram - MASTER LED 6.5-50W 927  
MR16 60D Dim



Accent Diagram - MASTER LED 6.5-50W 940  
MR16 60D Dim




Accent Diagram - MASTER LED 6.5-50W 927  
MR16 36D CN




Accent Diagram - MASTER LED 6.5-50W 927  
MR16 24D CN


## Beam Diagrams




Beam diagram - MASTER LED 6.5-50W 940  
MR16 36D Dim CN




Beam diagram - MASTER LED 6.5-50W 930  
MR16 36D Dim CN




Beam diagram - MASTER LED 6.5-50W 927  
MR16 60D Dim




Beam diagram - MASTER LED 6.5-50W 927  
MR16 10D Dim CN




Beam diagram - MASTER LED 6.5-50W 927  
MR16 24D Dim CN




Beam diagram - MASTER LED 7.5-50W+ 830  
MR16 24D Dim CN



Beam diagram - MASTER LED 6.5-50W 940  
MR16 24D Dim CN




Beam diagram - MASTER LED 7.5-50W+ 830  
MR16 36D Dim CN




Beam diagram - MASTER LED 6.5-50W 927  
MR16 36D CN

Beam Diagrams




Beam diagram - MASTER LED 6.5-50W 940 MR16 24D CN


Beam diagram - MASTER LED 6.5-50W 927 MR16 24D CN




Beam diagram - MASTER LED 6.5-50W 930 MR16 10D Dim CN




Beam diagram - MASTER LED 6.5-50W 940 MR16 10D Dim CN



Beam diagram - MASTER LED 6.5-50W 927 MR16 36D Dim CN



Beam diagram - MASTER LED 6.5-50W 930 MR16 24D Dim CN



Beam diagram - MASTER LED 6.5-50W 940 MR16 60D Dim

