



Extending the home feel onto the street

TownTune Central Post-Top DTC

As a luminaire family prepared for existing and scalable urban spaces, TownTune offers all the recent lighting innovations in terms of performance, quality of light and connectivity. The Philips TownTune family consists of three members: a central post top, an asymmetric spigot version and a version using an extending lyre post-top bracket. Each of these three can be customised with a choice of different shapes for housing and an optional decorative ring which comes in two colours. By having these options available, you can create your very own lighting signature and give a distinctive identity to districts and cities. The luminaire family is also equipped with the QR code-based Philips Service tag, which supports installation and maintenance work and enables you to create a digital library of lighting assets and spare parts. TownTune also makes use of the Philips Ledgine optimised lighting platform, ensuring that you always have the right amount and direction of light on your street. Furthermore, thanks to being SR (System-Ready), TownTune is also future-proof and is ready to be paired with both standalone and advanced control and lighting software applications, such as Interact City.

TownTune Central Post-Top DTC

Benefits

- It delivers visual comfort and comfortable lighting experiences in urban spaces through its dedicated designed bowl
- A simple, pure design, making it possible to integrate it into various urban environments and the option for customisation through a wide range of accessories, lets cities create a unique light signature, which can also become part of the urban furniture in the daytime
- It has a wide application coverage and offers great performance by using the latest Ledgine LED platform and providing access to a wide range of light distributions
- Ready to be paired with lighting control and software applications, by being equipped with the Philips SR (System Ready) socket
- Equipped with a service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Features

- Optimised Total Cost of Ownership and option of CLO (Constant Light Output)
- Excellent quality of light enabled by the Philips Ledgine optimised platform, and further optimisation in L-Tune is also possible
- Choice of different shapes for housing (cone, dome), option of decorative ring and colours (clear and golden)
- Ready to be paired with standalone lighting controls such as LumiStep, DynaDimmer and LineSwitch, and advanced system and software applications, such as Interact City
- Wide choice of lumen packages, ranging from 1,200 to 10,000 lumens
- Choice of colour temperature: 3,000 K (warm white) or 4,000 K (neutral white)
- Long lifetime of 100,000 hours at minimum L85
- Access to the gear via the gear cover on top of the luminaire
- Suitable for new and retrofit installations
- Vandal-resistant (IK10), and high ingress protection (IP66)

Application

- Urban and residential areas
- Cycle paths, footpaths and pedestrian crossings
- City centers and squares
- Car parks

Versions



TownTune Central Post-Top DTC

Product details

TownTune CPT DR BDP261



TownTune CPT DTC BDP262



Accessories

Ordercode 49034800



TownTune Central Post-Top DTC

Application Conditions

Maximum dim level	10%
-------------------	-----

Approval and Application

Mech. impact protection code	IK10
Surge Protection (Common/Differential)	Philips standard surge protection level kV

Controls and Dimming

Dimmable	Yes
----------	-----

General Information

CE mark	CE mark
Optical cover/lens type	PC-UV
Driver included	Yes
Flammability mark	F
Light source replaceable	Yes
Number of gear units	1 unit
Product Family Code	BDP262

Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Upward light output ratio	0

Mechanical and Housing

Colour	Dark Grey
--------	-----------

General Information

Order Code	Full Product Name	Luminaire light beam	Light source	Lamp	Optic type
		spread	colour	family code	
49026300	BDP262 LED59-4S/830 II	23° - 8° x 152°	830 warm	LED59	Distribution wide
	DW50 DR CLO LS-6		white		50
49030000	BDP262 LED24-4S/740 II	4° - 57° x 149°	740 neutral	LED24	Distribution
	DM33 CLO SRTB 62P		white		medium 33

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour	Init. Colour	Initial luminous flux
		Temperature	Rendering Index	
49026300	BDP262 LED59-4S/830 II DW50 DR CLO LS-6	3000 K	>80	3886 lm

Order Code	Full Product Name	Init. Corr. Colour	Init. Colour	Initial luminous flux
		Temperature	Rendering Index	
49030000	BDP262 LED24-4S/740 II DM33 CLO SRTB 62P	4000 K	>70	1725 lm

