



Switch light settings without switching spots

SceneSwitch LEDspot

Some situations call for cool light, others benefit from the ambience of a warm, cosy glow. With Philips SceneSwitch LEDspot, you can have different light settings from just one spot. And you don't need a dimmer! Optimise your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Auto memory: recall your last setting automatically

Features

- Multiple light settings in one lamp
- Plug and play
- Built-in memory chip

Application


- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)
- Accent and general lighting (e.g. hotels, shops and offices)

SceneSwitch LEDspot


Versions




Dimensional drawing



Product	D	C
LED SceneSwitch 50W GU10 WW-CW 36D ND 1BC/6	50 mm	54 mm




Accent Diagrams



LEDspot SSW 50W GU10 PAR16 827-840 36D
ND

Beam Diagrams



LEDspot SSW 50W GU10 PAR16 827-840 36D
ND

