



Switch light settings without switching spots

SceneSwitch LEDspot

Some situations call for cool light, others benefit from the ambience of a warm, cosy glow. With Philips SceneSwitch LEDspot, you can have different light settings from just one spot. And you don't need a dimmer! Optimise your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Auto memory: recall your last setting automatically

Features

- Multiple light settings in one lamp
- Plug and play
- Built-in memory chip

Application


- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)
- Accent and general lighting (e.g. hotels, shops and offices)

SceneSwitch LEDspot

Versions



Dimensional drawing



Product	D	C
LED Scene Switch LEDSSW 4.5-50W GU10 827 36D 1BC/3	50 mm	54 mm
LED SSW 50W GU10 WH-CDL 36D ND	50 mm	54 mm
LED Scene Switch LED SSW 50W GU10 WW-CW 36D ND 1BC/6	50 mm	54 mm

SceneSwitch LEDspot

Approval and Application

Energy Consumption kWh/1000 h	5 kWh
Energy Efficiency Label (EEL)	A+

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V

General Information

Cap-Base	GU10
Nominal Lifetime (Nom)	15000 h
Rated Lifetime (Hours)	15000 h
Switching Cycle	50000X

Light Technical

Beam Angle (Nom)	36 °
Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Rated Beam Angle	36 °

Mechanical and Housing

Bulb Shape	PAR16
------------	-------

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)	Starting Time (Nom)
929001346019	LED Scene Switch LEDSSW 4.5-50W GU10 827 36D 1BC/3	-	0.5 s
929001894501	LED Scene Switch LED SSW 50W GU10 WW-CW 36D ND 1BC/6	-	0.4 s
929001894607	LED Scene Switch LED SSW 50W GU10 WH-CDL 36D ND	5 W	0.4 s

Light Technical



Order Code	Full Product Name	Colour Code	Correlated		
			Colour Temperature (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
929001346019	LED Scene Switch LEDSSW 4.5-50W GU10 827 36D 1BC/3	827/825/822	-	-	600 cd
929001894501	LED Scene Switch LED SSW 50W GU10 WW-CW 36D ND 1BC/6	827/840	-	-	700 cd

Order Code	Full Product Name	Colour Code	Correlated		
			Colour Temperature (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
929001894607	LED Scene Switch LED SSW 50W GU10 WH-CDL 36D ND	865/830	3000/6500 K	450 lm	700 cd



Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001346019	LED Scene Switch LEDSSW 4.5-50W GU10 827 36D 1BC/3	80 °C
929001894501	LED Scene Switch LED SSW 50W GU10 WW-CW 36D ND 1BC/6	85 °C
929001894607	LED Scene Switch LED SSW 50W GU10 WH-CDL 36D ND	85 °C

SceneSwitch LEDspot





Accent Diagrams



SceneSwitch LED Lamps 50W GU10 827 36D SSW

LEDspot SSW 50W GU10 PAR16 827-840 36D ND

Beam Diagrams



SceneSwitch LED Lamps 50W GU10 827 36D SSW

LEDspot SSW 50W GU10 PAR16 827-840 36D ND

