



# Switch light settings without switching lamp

## SceneSwitch LED candles and lusters

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LED candles and lusters you can have different light settings from just one lamp. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

### Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Auto memory: recall your last setting automatically

### Features

- Multiple light settings in one lamp
- Plug and play
- Built-in memory chip

### Application

- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)
- Accent and general lighting (e.g. hotels, shops and offices)


# SceneSwitch LED candles and lusters

## Versions



E14 B38 Clear

## Dimensional drawing



Product	D	C
LED Scene Switch 40W B38 E14 WW CL ND 2CT/4	38 mm	113 mm
LED SSW 40W B38 E14 WW CL ND RF 1BC/6	38 mm	113 mm
LED SSW 40W B38 E14 WW CL ND 1SRT4	38 mm	113 mm

